

415V Simple Selection Table

Follow this table for easy steps to your part number. If you know your PDU type and your input plug, you can find your part number.

415V, 30A, 3 Phase Wye, G5 PDUs for North America. Feature (6) 20A 10kAIC Circuit Breakers.

Form Factor	Outlet Count	Outlet Type	NEMA L22-30P (IP20)	IEC 60309 3P+N+E 6h 30A (IP67)	IEC 60309 3P+N+E 6h 30A (IP44)
Basic Type PDU					
1U	6	(6)C19	P06B04M	P06B01M	P06B05M
0U FULL	24	(12)C13, (12)C19	P24B02M	P24B01M	P24B03M
0U FULL	36	(24)C13, (12)C19	P36B02M	P36B01M	P36B03M
0U FULL – 2 Sided	48	(36)C13, (12)C19	P48B02M	P48B01M	P48B07M
0U FULL – Wide	48	(48)C13	P48B03M	P48B04M	P48B08M
0U FULL – Wide	54	(48)C13, (6)C19	P54B03M	P54B01M	P54B02M
Monitored Input Type PDU					
1U	6	(6)C19	P06D02M	P06D01M	P06D03M
0U FULL	24	(12)C13, (12)C19	P24D04M	P24D02M	P24D05M
0U FULL	36	(24)C13, (12)C19	P36D02M	P36D01M	P36D03M
0U FULL – 2 Sided	48	(36)C13, (12)C19	P48D02M	P48D01M	P48D07M
0U FULL – Wide	48	(48)C13	P48D03M	P48D04M	P48D08M
0U FULL +	42	(36)C13, (6)C19	P42D07M	P42D05M	P42D08M
Monitored Switched Type PDU					
0U FULL	24	(12)C13, (12)C19	P24E06M	P24E05M	P24E09M
0U FULL	24	(18)C13, (6)C19	P24E12M	P24E07M	P24E10M
0U FULL	24	(24)C13	P24E13M	P24E08M	P24E11M
0U FULL – Wide	36	(24)C13, (12)C19	P36E02M	P36E01M	P36E04M
0U FULL – Wide	36	(30)C13, (6)C19	P36E06M	P36E03M	P36E05M
0U FULL – 2 Sided	48	(36)C13, (12)C19	P48E02M	P48E01M	P48E08M
0U FULL – 2 Sided	48	(48)C13	P48E14M	P48E07M	P48E09M
0U FULL – Wide +	48	(48)C13	P48E04M	P48E03M	P48E11M
0U FULL – Wide +	48	(42)C13, (6)C19	P48E06M	P48E05M	P48E12M
Monitored Per Outlet Type PDU					
0U FULL	24	(12)C13, (12)C19	P24F10M	P24F09M	P24F13M
0U FULL	24	(18)C13, (6)C19	P24F16M	P24F11M	P24F14M
0U FULL	24	(24)C13	P24F17M	P24F12M	P24F15M
0U FULL – Wide	36	(24)C13, (12)C19	P36F02M	P36F01M	P36F04M
0U FULL – Wide	36	(30)C13, (6)C19	P36F06M	P36F03M	P36F05M
0U FULL – 2 Sided	48	(36)C13, (12)C19	P48F02M	P48F01M	P48F08M
0U FULL – 2 Sided	48	(48)C13	P48F10M	P48F07M	P48F13M
0U FULL – Wide +	48	(48)C13	P48F04M	P48F03M	P48F11M
0U FULL – Wide +	48	(42)C13, (6)C19	P48F06M	P48F05M	P48F12M
Monitored and Switched Per Outlet Type PDU					
0U FULL	24	(12)C13, (12)C19	P24G10M	P24G09M	P24G15M
0U FULL	24	(18)C13, (6)C19	P24G18M	P24G13M	P24G16M
0U FULL	24	(24)C13	P24G19M	P24G14M	P24G17M
0U FULL – Wide	36	(24)C13, (12)C19	P36G02M	P36G01M	P36G04M
0U FULL – Wide	36	(30)C13, (6)C19	P36G06M	P36G03M	P36G05M
0U FULL – 2 Sided	48	(36)C13, (12)C19	P48G02M	P48G01M	P48G08M
0U FULL – 2 Sided	48	(48)C13	P48G11M	P48G07M	P48G10M
0U FULL – Wide +	48	(48)C13	P48G04M	P48G03M	P48G12M
0U FULL – Wide +	48	(42)C13, (6)C19	P48G06M	P48G05M	P48G13M

Note: MOQ 30 & LT 20 Business Days applies for all 415V PDUs for North America.