

4

D

C

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	۳۳ A ۳۳		× = = ×			** C **			
	TYPE	COLOR	TYPE	COLOR	── DIM "L" (mm∕IN)	COLOR	DESCRIPTION		
NPCA01-X	C14	RED	C13	RED	24"/609.6mm	RED	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK, F		
NPCA02-X	C14	RED	C13	RED	48"/1,219.2mm	RED	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK,		
NPCA03-X	C14	RED	C13	RED	72"/1,828.8mm	RED	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK,		
NPCA04-X	C14	RED	C13	RED	96"/2,438.4mm	RED	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK,		
NPCA05-X	C14	RED	C13	RED	120"/3,048mm	RED	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK,		
NPCA06-X	C14	BLUE	C13	BLUE	24"/609.6mm	BLUE	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK,		
NPCA07-X	C14	BLUE	C13	BLUE	48"/1,219.2mm	BLUE	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK,		
NPCA08-X	C14	BLUE	C13	BLUE	72"/1,828.8mm	BLUE	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK,		
NPCA09-X	C14	BLUE	C13	BLUE	96"/2,438.4mm	BLUE	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK,		
NPCA10-X	C14	BLUE	C13	BLUE	120"/3,048mm	BLUE	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK,		
NPCA11-X	C14	BLACK	C13	BLACK	24"/609.6mm	BLACK	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 2 FEET, 10 PK, E		
NPCA12-X	C14	BLACK	C13	BLACK	48"/1,219.2mm	BLACK	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 4 FEET, 10 PK, E		
NPCA13-X	C14	BLACK	C13	BLACK	72"/1,828.8mm	BLACK	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 6 FEET, 10 PK, E		
NPCA14-X	C14	BLACK	C13	BLACK	96"/2,438.4mm	BLACK	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 8 FEET, 10 PK, E		
NPCA15-X	C14	BLACK	C13	BLACK	120"/3,048mm	BLACK	NON-LOCKING POWER CORD, IEC C14 TO IEC C13, 10 FEET, 10 PK, E		
NPCB01-X	C20	RED	C19	RED	24"/609.6mm	RED	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK,		
NPCB02-X	C20	RED	C19	RED	48"/1,219.2mm	RED	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK,		
NPCB03-X	C20	RED	C19	RED	72"/1,828.8mm	RED	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK,		
NPCB04-X	C20	RED	C19	RED	96"/2,438.4mm	RED	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK,		
NPCB05-X	C20	RED	C19	RED	120"/3,048mm	RED	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK,		
NPCB06-X	C20	BLUE	C19	BLUE	24"/609.6mm	BLUE	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK,		
NPCB07-X	C20	BLUE	C19	BLUE	48"/1,219.2mm	BLUE	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK,		
NPCB08-X	C20	BLUE	C19	BLUE	72"/1,828.8mm	BLUE	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK,		
NPCB09-X	C20	BLUE	C19	BLUE	96"/2,438.4mm	BLUE	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK,		
NPCB10-X	C20	BLUE	C19	BLUE	120"/3,048mm	BLUE	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK,		
NPCB11-X	C20	BLACK	C19	BLACK	24‴/609.6mm	BLACK	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 2 FEET, 10 PK, E		
NPCB12-X	C20	BLACK	C19	BLACK	48"/1,219.2mm	BLACK	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 4 FEET, 10 PK, E		
NPCB13-X	C20	BLACK	C19	BLACK	72"/1,828.8mm	BLACK	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 6 FEET, 10 PK, E		
NPCB14-X	C20	BLACK	C19	BLACK	96"/2,438.4mm	BLACK	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 8 FEET, 10 PK, E		
NPCB15-X	C20	BLACK	C19	BLACK	120"/3,048mm	BLACK	NON-LOCKING POWER CORD, IEC C20 TO IEC C19, 10 FEET, 10 PK, E		

3		2	
			NOTES: 1. IDENTIFICAT
→	SEE "B" IN TABLE		<u>part no.</u> See table
· / ·			2. PART SPECIF RATING: C14. C20.
			CABLE: SJT 3. Rohs Compli 4. Compliance
			KC, CE, UL U N/14877 OR U 5. primary dimu

00A	04/16/2021	PJST	GLM	JAWI	RELEASED TO PR
REV	DATE	BY	снк	APR	

ATION: NON-LOCKING POWER CORDS

TABLE AT SPECIFICATION: ATING: C14/C13 - 10A / 250V AC C20/C19 - 16A / 250V AC CABLE: SJT AND HOSVV-F (17AWG OR EQUAVALENT) 3 CONDUCTOR, 105°C RoHS COMPLIANT. COMPLIANCE APPROVALS: KC, CE, UL OR c(UL)US, ENEC, VDE, PSE, CCCS, NSW22009, CCC, N/14877 OR NSW22012 5. PRIMARY DIMENSIONS ARE IN INCHES, SECONDARY DIMENSIONS ARE IN [MILLIMETERS]

			AT YOU CHECK S, NOTES, AND BOX. ILL NOT PROGR PROVAL. PLEAS ING PROOF AS							
		TITLE	Ν			WER CORD				
		ITEM REVISIO			JSTOMER DR.					
		02416NPC/00								
			E NAME 024							
		UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			N/A					
		.X ± .XX ±		.XXX ±						
RODUCTION	02416NPC			тн	IRD ANGLE OJECTION	DRAWING NUMBERI 02416NPC_DC				
DESCRIPTION	ECN	DRAWN BY D	ATE 04/16/2021	снк GLM	SCALE NTS	SHT 1 OF 1	:)			
	•					•				

1