


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
PZRFE12U	17.6 LB/EACH PC (8.00 kg/EACH PC)



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. UL 2043 REQUIRED FOR USE IN PLENUM SPACE.
5. PART INCLUDES:
 - 1- ENCLOSURE
 - 4- PEDISTAL SUPPORT MOUNTING BRACKETS
 - 4- NYLON CABLE SLEEVES
 - 1- MAGNETIC RULER

UTILIZES PANDUIT
NYLON CABLE
SLEEVE ASSEMBLIES



PATENTED DESIGN
SUPPORT MOUNT BRACKETS
(4X) ATTACH TO THE
RAISED FLOOR PEDESTALS
PROVIDE SINGLE TILE DROP
IN REDUCING INSTALLATION
BY 50%




TITLE		PANZONE RAISED FLOOR ENCLOSURE 12 RACK SPACES (PZRFE12U)	
CUSTOMER DRAWING			
ITEM REVISION NAME		V10560AJ/00	
DATASET FILE NAME		V10560AJ_DC/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL:	
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007		METRIC - MILLIMETER X +/- 0.8 X.X +/- 0.46 X.XX +/- 0.18	
ANGLE +/- 1°			
THIRD ANGLE PROJECTION		DRAWING NUMBER: V10560AJ	
DRAWN BY BAME	DATE 5-19-10	CHK RYB	SCALE NONE
SHT 1 OF 2		SIZE A	


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

EACH ENCLOSURE CAN ACCOMMODATE BOTH FIELD TERMINATED OR PRE-TERMINATED CONNECTIVITY. IF USING FIELD TERMINATED CONNECTIVITY LEAVE TIA/EIA 19" MOUNTING BRACKETS AS FACTORY INSTALLED OR REMOVED CENTER MOUNTING BRACKET (SEE VIEW 1 AND 2). IF USING PRE-TERMINATED CONNECTIVITY (EXAMPLE: CASSETTES, ENCLOSURES) REMOVE TIA/EIA 19" MOUNTING BRACKETS AND RELOCATE TO THE CENTER OF THE ENCLOSURE (SEE VIEW 3)


VIEW 1



VIEW 2



VIEW 3



6 RACK SPACE
CONFIGURATION

										TITLE <div>PANZONE RAISED FLOOR ENCLOSURE 12 RACK SPACES (PZRFE12U) CUSTOMER DRAWING</div>			
										ITEM REVISION NAME V10560AJ/00		<div>PANDUIT</div>	
										DATASET FILE NAME V10560AJ_DC/00B			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007		MATERIAL: <	