NetKey[™] Category 6 UTP Patch Cords

North America, Latin America, Europe, Middle East, Africa



SPECIFICATIONS

Category 6/Class E patch cords shall be constructed of UTP 24 AWG stranded copper cable and a modular plug at each end. Patch cords shall be used in all work area outlets and patch panels. Patch cords shall be wired to be compatible with both T568A and T568B wiring schemes.



TECHNICAL INFORMATION

Category 6/Class E channel performance:	Exceeds ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E channel requirements at swept frequencies up to 250 MHz Meets ANSI/TIA-568.2-D and ISO 11801 Category 6 component requirements at swept frequencies up to 250 MHz◊
Cable diameter:	0.235 in. (6.0mm) nominal
FCC compliance:	Complies with ANSI/TIA-1096-A (formerly FCC Part 68); contacts plated with 50 microinches of gold
IEC compliance:	Meets IEC 60603-7
PoE compliance:	Supports IEEE 802.3af/802.3at and 802.3bt type 3 and type 4 PoE applications
Safety compliance:	cULus Listed; UL 1863 and CAN/CSA-C22.2 (UL File E129886)
RoHS compliance:	Compliant
Flammability rating:	CM rated

KEY FEATURES AND BENEFITS

100% Performance tested:	Confidence that each patch cord delivers specified performance
Patented tangle-free latch:	Prevents snags and provides easy release
Slender strain relief boot:	Provides easy access in high-density applications
Identification:	Provides identification of performance level, length, and quality control number for future traceability

APPLICATIONS

Applications include:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), and 1000BASE-T (Gigabit Ethernet)
- 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM
- Token Ring 4/16
- Voice over internet protocol (VoIP)

NetKey Category 6 UTP Patch Cords

Foot lengths: NK6PC*^Y Meter lengths: NK6PC**M^Y

NetKey Category 6 UTP Jack Modules

TG style module: NK688M^^

NetKey Patch Panels with Labels

24-port, 1 RU (with 6 NK4MFL):

NKFPL24

48-port, 2 RU (with 12 NK4MFL):

NKFPL48

NetKey Patch Panels without Labels

24-port, 1 RU (with 6 NK4MFL):

NKFPA24

48-port, 2 RU (with 12 NK4MFL):

NKFPA48

Strain Relief Bars

Straight: SRBS19BL-XY Extended 2": SRB19BLY

With hook and

loop ties:

SRBM19BLY

With adjustable clips:

SRBWCY

Deep, 5": Deep, 7": SRB19D5BL SRB19D7BL

Multi-depth:

SRB19MDBL


*Foot Lengths: 1-20, 25, 30, 35, 40, 45, 50 ft. **Meter Lengths: 1-5, 7, 10, 15, 20 meters ^Colors other than Off White: BU (Blue), BL (Black), RD (Red), YL (Yellow), GY (Gray), GR (Green), OR (Orange), VL (Violet)

A^Colors: BU (Blue), BL (Black), WH (White), GR (Green), RD (Red), YL (Yellow), IG (International Gray), El (Electric Ivory), IW (Off White)

◊Lengths 1m to 15m or 1 foot to 49 feet are guaranteed to meet TIA and ISO component and channel requirements. Lengths greater than 15m or 49 feet are guaranteed to meet ISO component and both TIA and ISO channel requirements.

NetKey[™] Category 6 UTP Patch Cords

ENGINEERING DRAWING



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

