Material			High Conductivity Seamless Copper Tube						
Plating			Electro-Tin						
Wire Size			2 AWG					.47 R REF	
Wire Type			Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric						
Wire Strip Length		l	1-1/4 in.			P∧ B	$\checkmark$		
Stud Size			3/8 in.						
UL Listed Wire Connector			Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		.36±.0441±.02 DIA				
UL Temperature Rating			90° C						
C.S.A Certified Wire Connector			Yes		Beveled wire entry .42±.01 .31±.01				
Panduit Color Code on Barrel		ode	BROWN						
Panduit Die Index No. on Barrel		x No.	P33						
Alternate Industry Die Index No. ( ) on Barrel			(10)		Wire inspection window				
		<b>B</b> <sup>®</sup>					<u> </u>	45°±5°	
	CE	RTIFIED	USTED Wire Connector	.10 <u>+</u>	01	-		1.88 REF	
		1			1				
								CORP. TINLEY PARK, ILLINOIS	
								LCB2-38WH-Q Copper Lug - One-Hole Long Barrel with Window 45° Angle Tongue	
0 4/17 JHNU JHNU			DRAWING RELEASED		019765		RGB		
V DATE	BY	СНК	DESCRIPTION		ECN	-R	SUP	SCALE DRAWING NO / CAD FILE LCB2-38WH-CUST	