

Part Number: P512HDT

Product Description: ADJUSTABLE BOX BAR HANGER - INCLUDES 3/8" STUD TO ACCOMMODATE FIXTURE STEMS



Material Specifications

Type: Pre-Galvanized Steel

Finish: Pre-Galvanized

Color: Silver

Function Specifications

Compatible Wires and Cables

AC/MC CABLE (OD):
Drop Wire:
Plain Rod (in):

Threaded Rods and Bolts

Tapped Holes:
Clearance Holes (in): Mounting Holes for screws/nails
Threaded Rod Size (in):

Compatible Conduit

EMT Size (in):
Rigid/IMC (in):

Compatible Flanges and Studs

Flange Size (in):
Metal Stud Size (ins): Most standard 1-3/8" width

Static Load Rating

Vertical (lbs):
Horizontal (lbs):

Other

16"-24" Length, Includes clip that attaches to 1/2" knockouts on the bottom of boxes

Codes and Regulatory

Regulatory Certifications: -

Country of Origin: CN

Packaging

General Packaging: Cardboard Box
Box Size: 23.25 X 6.25 X 9.5

Pieces per Package: 50
Other Box Features:

Document Information

Created By: DBLA
Checked By: DJW
Approved By: KLN

Customer Specification #: C11403
Revision Level: 01
ECN #: GAECN01482
Date: 12/10/2013