


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	WEIGHT
FWR-C	.80 LB/100 PCS (360 g/100 PCS)

NOTES:

- * 1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- 2. THIS PART ACCOMMODATES NARROW SLOTTED "F" AND "HN" DUCT WIDTHS: 1.50(38.1), 2.00(50.8), 3.00(76.2), AND 4.00(101.6).
- 3. THIS PART ALSO PROVIDES AS AN "F" AND "HN" DUCT LABELING DEVICE AS SHOWN IN DETAIL "A". USED TO IDENTIFY BOTH WIRES EXITING DUCT AND ADJACENT TERMINATIONS.
- 4. DIMENSIONS IN PARENTHESES ARE IN METRIC.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02	04.14.22	BDK	MRJS	MSAD	B: MATERIAL WAS "POLYVINYL CHLORIDE"	120076

<p>TITLE</p> <p align="center">WIRE RETAINER (FWR-C) FOR NARROW SLOTTED "F" & "HN" DUCT</p> <p align="center">CONTROL DRAWING</p>					
<p>ITEM REVISION NAME</p> <p align="center">D34518EI/00</p>					
<p>DATASET FILE NAME</p> <p align="center">D34518EI_DC_FWR/00C</p>					
<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]</p> <p>.x ± .xxx ± .010 [.3]</p> <p>.xx ± .03 [.8] ANGLS ±</p>					<p>MATERIAL:</p> <p align="center">△ B PC/ABS</p>
<p>THIRD ANGLE PROJECTION</p>					<p>DRAWING NUMBER:</p> <p align="center">34518-34</p>
<p>DRAWN BY</p> <p>DW</p>	<p>DATE</p> <p>1-21-94</p>	<p>CHK</p> <p>CEF</p>	<p>SCALE</p> <p>NONE</p>	<p>SHT 1 OF 1</p>	<p>SIZE</p> <p>A</p>

D10.100DA/20