						2		1	
		THIS CO	PY IS	5 PRO'	/ I DEC	ON A RESTRICTED BASIS AND IS NOT TO BE US	ed in any w	AY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. PANDUIT P/N WEIGHT CP48HDBL 6.15 LB/10 PCS (2788.0 g/10 PCS	
B		25 – 1 . 8]	1				1.04 [26.4]	NOTES: 1. SEE CURRENT CATALOG FOR VAROUS APPLICATIONS WITH THIS WIRING SYSTEM 2. THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS. 3. PACKAGE CONTAINS: (1) 48 PORT STAMPING (6) 8 POSITION FACEPLATES (ASSEMBLED TO PANEL) (6) GROUNDING STRIPS (ASSEMBLED TO PANEL) (1) SCREW KIT (INCLUDES FOUR #12-24 SCREWS) (2) M6 GROUNDING SCREWS (2) #12-24 GROUNDING SCREWS 4. DIMENSION IN (1) ARE IN METRIC.	В
Ļ		.62 -				18.20 [462.3] [482.6]		PART NUMBER	~~~
								CP48HDBL N/A	
A								MINI-COM 48 PORT HIGH DENSITY SHIELDED MODULAR PATCH PANEL	A
								CUSTOMER DRAWING	
								11M249AQ/02.PRT DATASET FILE NAME 11M249AQ_DC/02A.PRT	
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] STAMPING-18 GAUGE STAINLESS STEEL	
	1	11–13–18	BAME	KRKE	MMR	A. REMOVED METRIC MOUNTING SCREWS	11M249AQ-02	X ± .XXX ± .010 [.3] GROUNDING STRIP- PHOS BRONZE .XX ± .03 [.8] ANGLES ± FACEPLATE-ABS	
	R	11-26-12	BJN	JSP	JSP	RELEASED TO PRODUCTION	11M249AQ-02	THIRD ANGLE DRAWING NUMBER: PROJECTION 11M249AQ-02	
	REV	DATE	ΒY	СНК	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE SIZE BJN 11-26-12 JSP NONE SHT 1 0F 1 A	
	1					2		1	