2		1			
THIS COPY IS PROVIDED ON A RESTRICTED E	BASIS AND IS NOT TO BE USE	ed in any w	AY DETRIMENTAL TO THE INTE	RESTS OF PANDUIT CORP.	
			PANDUIT P/N	WEIGHT	
◀──── 4.50 ───►			UICFPSE8**-2G	1.00 LB/10 PCS. (454.4 G/10 PCS.)	
[114.3] B 4.50		.85 1.6]	PART NUMBER SUF COLOR AND OR PA 2. SEE CATALOG FOR PARTS APPLICABL PART. 3. DIMENSIONS IN P METRIC. 4. PART INCLUDES: 1 - FACEPLATE	ALOG FOR ADDITIONAL FIXES TO INDICATE CKAGE QUANTITY. COMPLETE LIST OF E FOR USE WITH THIS ARENTHESES ARE IN NATED LABEL COVER COVER	B
				SE8**-2G	
A			MINI-COM ULTIMATE ID 8 POSITION EXECUTIVE SLOPED DOUBLE GANG FACEPLATE CUSTOMER DRAWING		
			ITEM REVISION NAME		
			DATASET FILE NAME M01739BD_DC/03A	PANDUIT	
			UNLESS OTHERWISE SPECIFIE DIMENSIONAL TOLERANCES ARE:	[N [mm]	
			.x ± .01C .xx ± .03[.8] ANGLES ±	ABS	
1 5-14-14 BJN JSP MMR REVISED & REDRAWN PREV	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY 017		THIRD A	NGLE 01739-02	
1 5-14-14 BJN JSP MMR REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY REV DATE BY CHK APR DESCRIPTION		ECN	DRAWN BY DATE CHK SCALE	FULL SHT 1 OF 1	
2			1		