					2		1
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT							
							PANDUIT P/N WEIGHT
							CPPLA72WBLY .72 LB/EACH PC (323.1 g/EACH PC)
	2.38 – [60.3]		3.9 .99. _★			4.26 [108.1	NOTES: 1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM. 2. THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS. 3. PACKAGE CONTENTS: (1) -72 PORT STAMPING (6) -12 POSITION FACEPLATE WITH LABEL SLOTS (1) -SCREW KIT (INCLUDES FOUR #12-24 SCREWS) (18) -LABEL COVER (19) -LABEL COVER (11) -LABEL SHEET (INCLUDES 18 PRE-PRINTED LABELS) 4. PATCH PANELS ACCEPT SNAP-IN MINI-COM MODULES. 5. DIMENSIONS IN PARENTHESIS
Ţ		1.25] 52 —			3.47 (88.1)	ARE IN METRIC.
A			5.9]		[482.6]	Â	PART NUMBER CPPLA72WBLY TITLE MINI-COM 72 PORT ANGLED MODULAR FACEPLATE PATCH PANEL WITH LABEL/COVER CUSTOMER DRAWING ITEM REVISION NAME M02479CQ/00 DATASET FILE NAME M02479CQ DC70/00D
							MID2473CQ_DC70700D
2	11-8-18		KRKE		B. REMOVED METRIC SCREWS	02479-070	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .xxx ± .010[.3] FACEPLATES; ABS
4 -	4-15-14	MDJR	REFR		A. UPDATED TITLE BLOCK	02479-070	.XX ± .03 [.8] ANGLES ±
*1790001010 REV	3–11–06	JSP	MJD	MJD	RELEASED TO PRODUCTION	02479-070	THIRD ANGLE PROJECTION 02479-070
	DATE	ΒY	СНК	APR	DESCRIPTION	ECN	JSP 3–11–06 MJD NONE SHT 1 OF 1
					2		1