





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- PAN-TY LOOP FOR
CABLE HOLD-DOWN
(4 PLACES)


COVER REMOVED FOR CLARITY



BREAKOUT AREA
(3 PLACES)

— KNOCK OUT
MOUNTING HOLES FOR
#6 PAN HEAD SCREW


POST FOR TAMPER
RESISTANT SCREW



NOTES :

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. ALSO INCLUDED WITH BOX:
 - 1- BOX BASE
 - 1- BOX COVER
 - 2- PLT1.5I-M PAN-TY
 - 1- LABEL/ LABEL COVER
 - 2- MOUNTING SCREW
 - 1- COVER SCREW (USED TO SECURE COVER TO BASE)
 - 2- STRIP OF 1.00" X .75" FOAM TAPE FOR MOUNTING
 - 1- STRIP OF 3.00" X .75" FOAM TAPE FOR MOUNTING
 - 2- BEND RADIUS CONTROL BRIDGE
5. BASE HAS TWO POCKETS FOR OPTIONAL MAGNET (CSBM-X)
6. BREAKOUTS DESIGNED TO ACCEPT LDS/LDPH5 OR LD10/LDPH10 RACEWAY.
7. BASE MATERIAL THICKNESS= .090(2.29 mm)

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

PART NUMBER		CBXSD6** - AY			
TITLE					
MINI-COM 6 POSITION SHUTTERED SURFACE MOUNT DEEP BOX					
CUSTOMER DRAWING					
ITEM REVISION NAME		M02479EW/00			
DATASET FILE NAME		M02479EW_DC129/00B			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03 [.8] ANGLES ±				MATERIAL : BOX: ABS DOORS: PC	
 THIRD ANGLE PROJECTION				DRAWING NUMBER: 02479-129	
DRAWN BY	DATE	CHK	SCALE	SIZE	
JSP	12-27-06	MJD	NONE	SHT 1 OF 1	
				A	