


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES :



1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
4. CABLE MEETS REQUIREMENTS OF EUROCLASS Eca PER EN 50575.
5. CABLE DECLARATION OF PERFORMANCE IS PAN-DOP-FB001.



CABLE DESCRIPTION			
FIBER OPTIC INDOOR-OUTDOOR CENTRAL TUBE CABLE			
PART NUMBERS AVAILABLE	FIBER TYPE	JACKET RATING	COLOR
FBCC908-40	SINGLEMODE 9/125um	LSZH	BLACK
FBCC608-40	MULTIMODE 62.5/125um	LSZH	BLACK
FBCC508-40	MULTIMODE 50/125um OM2	LSZH	BLACK
FBCCX08-40	MULTIMODE 50/125um OM3	LSZH	BLACK
FBCCZ08-40	MULTIMODE 50/125um OM4	LSZH	BLACK

TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS	BEND RADIUS	
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	INSTALLATION	LONG TERM
	100 mm (3.9 in)	60 mm (2.4 in)
SINGLEMODE MAXIMUM LOSS	TENSILE LOAD - LSZH RATED	
.75 dB/KM @ 1310nm .75 dB/KM @ 1500nm	INSTALLATION	LONG TERM
	1500 N (337.5 lbf)	700 N (157.5 lbf)
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-20°C TO +70°C -4°F TO +158°F	-20°C TO +70°C -4°F TO +158°F	-40°C TO +75°C -40°F TO +167°F

OOA	4/12/18	JSP	WMA	SKH	INITIAL RELEASE	M02432DS-DC-08
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					FIBER OPTIC INDOOR-OUTDOOR CABLE WITH 8 FIBERS IN A CENTRAL TUBE	
CUSTOMER DRAWING						
ITEM REVISION NAME						
M02432DS/01						
DATASET FILE NAME				PART NO. FBCC*08-40		
M02432DS_DC_08/01A						
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] $.X \pm .XXX \pm .010 [0.3]$ $.XX \pm .03 [0.8]$ ANGLES \pm				DRAWING NUMBER: M02432DS-DC-08		
 THIRD ANGLE PROJECTION						
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE
JSP	4/12/18	WMA	NONE			A