



ITEM NUMBER	PART NUMBER	DESCRIPTION	STANDARD PACKAGE QTY.
1	MP300	MP300 PRINTER	1
2	*MP300-ACS	120-240 VAC POWER SUPPLY MODULE WITH POWER CORD FOR NORTH AMERICA	1
3	*MP300-BATT	LITHIUM ION BATTERY	1
4	MP-USB	MP100/300 USB PRINTER CABLE	1
5	*S100X150VAM	MP CASSETTE, SELF-LAMINATING LABEL, VINYL, 1.00" W x 1.50" H, .50" PRINT ON AREA, CLEAR/ WHITE	1
6	IMPORTANT INFORMATION	PRINTED COPY OF IMPORTANT SAFETY INFORMATION SHEET	1
7	QUICK REFERENCE CARD	PRINTED COPY OF QUICK REFERENCE CARD IN THREE LANGUAGES (EN, FR, SP)	1
8	*MP300-CASE	HARD PLASTIC CARRYING CASE WITHOUT SLEEVE	1
9	MP300-MAGNET	SET OF TWO MAGNETIC ATTACHMENTS FOR MP300 PRINTER	1
10	BATTERY DIRECTIVE	BATTERY DIRECTIVE INSTRUCTIONS FOR LITHIUM ION BATTERY PACK	1
11	MPCORDS-KIT	POWER CORD KIT CONTAINING POWER CORD FOR EUROPE, UNITED KINGDOM AND AUSTRALIA	1

NOTES:
 1. * IN FRONT OF PART NUMBER DENOTES SELLABLE PANDUIT PART NUMBER.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02	1-21-2021	JSUN	RCMC	ALP	REMOVE * BEFORE MP300-MAGNET	094056/00
01	11-04-2020	JSUN	BRJO	KJM	ADD AUSTRALIA POWER CORD TO MPCORDS-KIT. UPDATE MPCORDS-KIT PICTURE	080135/01
00	10-29-19	TMSA	RSMC	JHAC	INITIAL RELEASE	080135/00

TITLE MP300/E PANDUIT MP300/E MOBILE THERMAL TRANSFER PRINTER		CUSTOMER DRAWING	
ITEM REVISION NAME 00406SBC/02		PANDUIT	
DATASET FILE NAME 00406SBC_DC/02			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: NONE	
.x : .1 [2.54] .xxx : .005 [.127] .xx : .01 [.25] ANGLES : 5 °		DRAWING NUMBER: 00406SBC_DC	
DRAWN BY TMSA	DATE 10-29-19	CHK JHAC	SCALE NTS
SHT 1 OF 1		SIZE B	

D10100DB/17