


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. PLENUM-RATED CABLES MEET THE REQUIREMENTS OF NFPA 262. RISER-RATED CABLES MEET THE REQUIREMENTS OF UL 1666.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



PLENUM			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
400 lbs (1800 N)	120 lbs (540 N)	10.8 in (27.5 cm)	5.4 in (13.8 cm)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	STORAGE/OPERATION		INSTALLATION
0.54" [13.9mm]	-40°F TO +176°F [-40°C TO +80°C]		32°F TO +140°F [0°C TO +60°C]
RISER RATED			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
600 lbs (2670 N)	180 lbs (800 N)	13.2 in (33.6 cm)	6.6 in (16.8 cm)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	STORAGE/OPERATION		INSTALLATION
0.66" [16.8mm]	-40°F TO +176°F [-40°C TO +80°C]		14°F TO +140°F [-10°C TO +60°C]

WEIGHT OF 2.5km REEL/BOX	
OFNP	OFNR
912.7 kg (2012.1 lbs)	993.7 kg (2190.7 lbs)

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	PART NO.	DRAWING NUMBER:	SIZE	
00	02-04-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055HZ-DC	36 FIBER INDOOR/OUTDOOR CABLE WITH 900µm BUFFERED FIBERS CUSTOMER DRAWING	M02055HZ/00	M02055HZ_DC/00A	SEE TABLE	M02055HZ-DC	A	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		DRAWING NUMBER:				
							.x ± .xxx ± .010 (0.3)		DRAWING NUMBER:				
							.xx ± .03 (0.8) ANGLES ±		DRAWING NUMBER:				
							THIRD ANGLE PROJECTION		DRAWING NUMBER:				
							DRAWN BY: SAT		DATE: 02-04-14		SHT 1 OF 2		A
							CHK: WMA		SCALE: NONE				

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PART NO.	DESCRIPTION	FLAME RATING	CABLE ATTENUATION
FSLP536	MULTIMODE 50/125 OM2 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSLR536		OFNR	
FSLP636	MULTIMODE 62.5/125 OM1 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSLR636		OFNR	
FOLPX36	MULTIMODE 50/125 OM3 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOLRX36		OFNR	
FOLPZ36	MULTIMODE 50/125 OM4 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOLRZ36		OFNR	
FSLP936	SINGLEMODE 9/125 INDOOR/OUTDOOR CABLE	OFNP	0.7dB/km @ 1310nm 0.7dB/km @ 1550nm
FSLR936		OFNR	

B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	PART NO.	DRAWING NUMBER	SIZE
00	02-04-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055HZ-DC	36 FIBER INDOOR/OUTDOOR CABLE WITH 900um BUFFERED FIBERS CUSTOMER DRAWING	M02055HZ/00	M02055HZ_DC/00A	SEE TABLE	M02055HZ-DC	A
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxx ± .010 (0.3) .xx ± .03 (0.8) ANGLES ±					
							 THIRD ANGLE PROJECTION					