



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CPP48FM6VNSBL	12.8 LB/10 PCS (5785.7 g/10 PCS)

- NOTES:
- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
  - THE FLUSH MOUNT PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
  - PACKAGE CONTENTS:
    - (1) - 48 PORT STAMPING
    - (4) - 12 POSITION FACEPLATE (ASSEMBLED TO PANEL)
    - (1) - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
    - (1) - SCREW KIT (INCLUDES FOUR M6 SCREWS)
  - DIMENSIONS IN PARENTHESIS ARE IN METRIC.



PART NUMBER CPP48FM6VNSBL	PRODUCT SPEC/PKG SPEC N/A
I.I. NUMBER N/A	WORK INSTRUCTION N/A

TITLE  
**MINI-COM 48 PORT FLUSH MOUNT MODULAR 6-PACK PATCH PANEL WITH VERTICAL NUMBERING SEQUENCE**  
 CUSTOMER DRAWING

ITEM REVISION NAME  
**M01667AF/01**

DATASET FILE NAME  
**M01667AF\_DC16/01A**

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)  
 .x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ]  
 .xx ± .01 [ .25 ]      ANGLES ± 5 °

**PANDUIT**

MATERIAL:  
**PANEL: 18 GAGE GALVANNEALED-BLACK PAINT WITH WHITE LETTERING**

DRAWING NUMBER:  
**01667-16**

DRAWN BY BJN	DATE 5-3-12	CHK JAV	SCALE N/A	SHT 1 OF 1	SIZE A
-----------------	----------------	------------	--------------	------------	-----------

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	1-9-14	BJN	JAV	MMR	P/N WAS NONSTANDARD BEFORE, MAKING NEW STANDARD P/N	01667-16
R	5-3-12	BJN	JAV	JAV	RELEASED TO PRODUCTION	01667-16

D10100DA/14

2

1

2

1