THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


GJS6120U

GJS6180U

PANDUIT	LENGTH IN [mm]		
PART NUMBER			
GJ\$660U	60.0 ± 1.0 [1524 ± 25]		
GJ\$696U	96.0 ± 1.0 [2438 ± 25]		

NOTES:

- 1. PART NUMBERS: GJS660U, GJS696U, GJS6120U, GJS6180U
- 2. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS



120.0 ± 1.0

[3048 ± 25] 180.0 ± 1.0

[4572 ± 25]

FACTORY CRIMPED #6 AWG JUMPER WIRE ASSEMBLY (QTY. 1) INCLUDES: LCC6-14JAW (QTY. 1)
#6 AWG WIRE - GREEN/YELLOW INSULATION

							SINGLE TERMINATION GROUND JUMPERS (GJS660U, GJS696U, GJS6180U) CUSTOMER DRAWING		
							ITEM REVISION NAME N41737BB/01		
							DATASET FILE NAME C41737_01.SLDDRW		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		
01	8/21	JHNU	JHNU	JADE	REMOVED 16mm FROM WIRE DESCRIPTION REVISED TITLE BLOCK	104433	.X ± .XXX ± N/A .XX ± ANGLES ±		
00	3/08	JHNU	JHNU	JHNU	DRAWING RELEASED		THIRD ANGLE PROJECTION DRAWING NUMBER C41737		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE JHNU 3/08 N/A N/A SHEET 1 OF 1 A		