



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ACTUAL SIZE

NOTES:


1. VISIT OUR ON-LINE CATALOG AT
WWW.PANDUIT.COM FOR A LIST OF
CURRENT PARTS APPLICABLE FOR
USE WITH THIS PRODUCT.
2. CONTENTS:
 - 1 - VARIANT 5 CAT6A RJ45 JACK INSERT
 - 1 - VARIANT 5 FIXED CONNECTOR JACK
INSERT ADAPTER
 - 1 - VARIANT 5 FIXED CONNECTOR HOUSING
WITH CLAMP
 - 1 - VARIANT 5 FIXED CONNECTOR GASKET
SEAL
 - 2 - CABLE TIES (NOT SHOWN ON PRINT)
2. MATERIALS:
 - BULKHEAD HOUSING - POWDER COATED DIECAST
ALUMINUM
 - GASKET - NBR (NITRILE RUBBER)
 - CLAMP - STAINLESS STEEL
 - ADAPTER - PC UL94V-0
3. COMPONENTS TO BE IP67 RATED WHEN
FULLY MATED
4. OPERATING TEMPERATURE: -40°C TO 70°C
5. CONNECTOR IS COMPLIANT WITH IEC 61076-3-106
STANDARDS.
6. PRIMARY DIMENSIONS ARE MILLIMETERS.

Technical drawing of a square part with dimensions and tolerances:

- Top horizontal dimension: 22 ± 0.2 [0.87 ± 0.008 SQ]
- Right vertical dimension: $30 \pm .1$ [1.181 $\pm .005$]
- Bottom horizontal dimension: $3.3 \pm .1$ [.130 $\pm .005$]
- Left vertical dimension: $2.5 R$ [.10]
- Feature: MAX

MOUNTING DIMENSIONS
WALL THICKNESS >1mm [0.039"]

PART NUMBER	DESCRIPTION	WEIGHT *
1AEBHV56XS	VARIANT 5 BULKHEAD FIXED CONNECTOR - RJ45 CAT6A JACK	0.124LB/EACH (56.4g/EACH)

PART NUMBER						I AEBHV56XS					
TITLE											
VARIANT 5 BULKHEAD FIXED CONNECTOR ASSEMBLY - RJ45 CAT6A JACK CUSTOMER DRAWING											
ITEM REVISION NAME						PANDUIT					
00122LAA/00											
DATASET FILE NAME						MATERIAL:					
00122LAA_DC02/00A											
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN] .X ± .XXX ± .XX ± ANGLES ±						SEE NOTES					
 <p>THIRD ANGLE PROJECTION</p>						DRAWING NUMBER: 00122LAA-02					
DRAWN BY	DATE	CHK	SCALE					SIZE			
BJN	6-15-16	ROJC	NONE	SHT 1 OF 1				A			