





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT P/N	WEIGHT
CFPDS2**Y	.60 LB/10 PCS (272.2 g/10 PCS)

NOTES:

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
  2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
  3. DIMENSIONS IN [ ] ARE IN METRIC.
  4. PART INCLUDES:
    - 1- SLOPED INSERT (CHS2\*\*)
    - 1- ADAPTER
    - 1- BEZEL
    - 2- MOUNTING SCREW
    - 2- HOLDING CLAMP
    - 1- LABEL
    - 1- LABEL COVER



PART NUMBER		CFPDS2**Y			
TITLE					
MINI-COM 2 POSITION DENMARK SLOPED INSERT FACEPLATE					
CUSTOMER DRAWING					
ITEM REVISION NAME		M02479GY/00			
DATASET FILE NAME		M02479GY_DC155/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]  .X ± .XXX ± .010 [ .3 ] .XX ± .03 [ .8 ] 				MATERIAL : INSERT- ABS ADAPTER- ABS BEZEL- ABS HOLDING CLAMP- CRS	
THIRD ANGLE PROJECTION				DRAWING NUMBER: 02479-155	
DRAWN BY	DATE	CHK	SCALE	SIZE	
JSP	3-18-06	PBD	NONE	SHT 1 OF 1	
				A	