ELECTRICAL SOLUTIONS



B1.

Cable Ties

B2. Cable

Accessories

B3. Stainless Steel Ties

C1.

Wiring Duct

Surface Raceway

СЗ. Abrasion Protection

(4. Cable Management

> D1. Terminals


D2. Power Connectors

D3. Grounding Connectors


E1. Labeling Systems

U Surface Raceway System

- UL and CSA rated 600 V; meets UL 5A and CSA C22.2 No. 62.1-03 standards; FT4 rated
- · Large cable capacity with aesthetically pleasing design
- Tamper resistant







	Part Number	Part Description	Raceway Size	Color‡	Length (Ft.)	Ctn. Qty.		
	TG-70 Raceway Base and Cover — PACKAGED TOGETHER							
	TG70IW8	Supplied with pre-punched mounting holes.	5.32" x 2.68" (135.0mm x 68.0mm)	Off White	8	32		
	TG70IW10				10	40		
	T-70/TG-70/T	win-70 Raceway Cover						
	T70CIW8	T-70, TG-70, or Twin-70 raceway cover in 8' and 10' lengths.		Off White	8	96		
	T70CIW10				10	120		
	TG Raceway Divider Wall							
	TGDW8	TG raceway divider wall. Snaps onto rails in TG raceway base to create separate channels. Must use wire retainers to		Gray	8	64		
	TGDW10				10	80		

T70C



‡For other colors replace IW	(Off White) with EI	(Electric Ivory).
Order number of feat require	d in multiplan of sta	adard carton aucontitu

Order number of feet required in multiples of standard carton quantity.

E2. Labels E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Lockout/ Tagout & Safety Solutions

> F. Index

· Compatible with NEMA standard faceplates or Pan-Way® Classic Series Snap-On Faceplates

Std.

- Transitions to Panduit T-45 and LD profile raceway
- Supplied with pre-punched mounting holes