THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PACKAGE CONTENTS COPPER WIRE ONLY ΩTY PACKAGE RETROFIT RUN AWG ITEM WEIGHT "CODE WIRE" ITEM PART NUMBER KIT ITEM DESCRIPTION ΙN LBS Class B or C Stranded PART NUMBER KIT [KG] MIN. MAX. PACKAGED SPLIT BOLT AND 6 VS-CKSB10-8 10 SOL 8 SOL 0.75 INSULATING COVER KIT VS-CKSB10-8 10 STR 8 STR [0.34]FERRULE 12 F80-20-M PACKAGED SPLIT BOLT AND 6 VS-CKSB6-2 6 SOL 2 SOL 1.23 INSULATING COVER KIT VS-CKSB6-2 2 STR 6 STR [0.56]**FERRULE** 12 F80-20-M PACKAGED SPLIT BOLT AND 6 VS-CKSB1-00 1.96 1 SOL INSULATING COVER KIT VS-CKSB1-00 2/0 STR 1 STR [0.89]

 B

NOTES, UNLESS OTHERWISE SPECIFIED:

 ${\sf B}$

- 1. DÍMENSIONS IN BRACKETS ARE METRIC.
- 2. REFER TO WWW.PANDUIT.COM FOR COMPLETE INSTALLATION REQUIREMENTS AND USAGE LIMITATIONS FOR PANDUIT SPLIT BOLTS AND INSULATING COVERS.
- 3. REFER TO WWW.PANDUIT.COM FOR COMPLETE INSTALLATION REQUIREMENTS
 AND USAGE LIMITATIONS FOR PANDUIT FERRULES.

FERRULE

12

F80-20-M

								TITLE
_								VS-CKSB Series VeriSafe Connector Kits
A								$oxedsymbol{oxed}$ (Packaged Split Bolt Connector and Insulating Cover Kits) $oldsymbol{oldsymbol{oldsymbol{\mathcal{L}}}}$
								CUSTOMER DRAWING
								1 TEM REVISION NAME 00080EAZ/00
								00080EAZ/00 DATASET FILE NAME 00080EAZ_DC/00
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
								.x : .1 [2.54] .xxx : .005 [.127] N/A
JA/20	00	9/12/2018	ВКА	JBN	BKA	RELEASED	040526	THIRD ANGLE PROJECTION DRAWING NUMBER: OOO80EAZ-DC
010100D	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	BKA 9/12/2018 BKA NONE SHT 1 OF 1
_						2		1