Material		High Conductivity Seamless Copper Tube	(#)	Wire inspection window
Plating		Electro-Tin	I II	
Wire Size Wire Type		2/0 AWG		
		Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length		1-9/16 in.	.50±.04	53±.02 DIA
Stud Size		1/2 in.		
UL Listed V Connecto		Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating		90° C	.13±.01 —	90°±5°
C.S.A Certified Wire Connector		Yes		
Panduit Color Code on Barrel		BLACK		2.15 PANDUIT REF
Panduit Die Index No. on Barrel		P45		1.50±.04
Alternate Industry Die Index No. ( ) on Barrel		(13)		BLACK DIE P45 (13)
	CERTIFIEE	D LISTED Wire Connector		.45±.01 .58±.01 1.91 REF
				CORP. TINLEY PARK, ILLINOI
- A/17				LCB2/0-12WF-X Copper Lug - One-Hole, Long Barrel with Window, 90° Angle Tongue
00 4/17 JHNU JHNU DRAWING RELEASED   REV DATE BY CHK DESCRIPTION		LEAJED	021775	