						6	2		BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. Type Package Style Description Color							
		THIS COP	Y IS	PROV I	DED 0	IN A RE	STRICTED BASIS A	AND IS NOT TO BE	USED IN ANY W) Insulation						
	f	Part Nur	mber		Vidth n. :.08	(mm)	Length ft. (m) +1.31 [0.4] 32 [0.1]	Thickness in. (mm) ±.002 [0.05]	Type Package St	yle	Descrip	otion				on
		ST23-075	5-306	BK ().75 19.	1]	30 [9]	.03 (0.76)		Roll Box	TCTŽO BLASK		Tape with L	_iner	BLA	CK
В	NOTES: 1. VISIT OUR ON-LINE CATALOG AT WWW FOR A LIST OF CURRENT PARTS APPL USE WITH THIS PRODUCT. 2. ALL MATERIALS AND COMPONENTS USE MATERIAL RESTRICTIONS OF RoHS (EID DIRECTIVE 2011/65/EU ON THE RESTRICTIONS OF ROHS (EID DIRECTIVE 2011/65/EU ON THE RESTRICTION COMMITTED AND AN AS PROPOSED ROHS TECHNICAL ADAPTATION COMMITTED AND AN ATERIAL: EPR RUBBER 4. TEMPERATURE RATING: 90°C CONTINUE 130°C EMERGET S. FOR USE UP TO 69kV. 6. MOISTURE, CORROSION, UV, AND CHEMATE COMPLIANT TO CALIFORNIA PROP. 65									D MEET THE UROPEAN RICTION OF D BY THE EE. OUS NCY OVERLOA	D. E					
\$					ΓAPE CKNE	iss —										
A	Stronghold High Voltage CUSTOMER ITEM REVISION NAME 00803EBZ/00 DATASET FILE NAME								oltage Rub	<i>"</i>						
ZE										.× ±		RWISE SPECIFIED, ERANCES ARE: IN [mm] .xxx : .005 [.127]		MATERIAL: SEE NOTE3		
AL_ASIZE	00	11/13/2020	JHNU	MCHD	JADE	INITIAL P	RELEASE		090033			THIF	RD ANGLE JECTION	DRAWING NUMBE	RIOSEBZ_	_DC
NXGLOBAL	REV	DATE	BY	СНК	APR		DESCRIP	TION	ECN	DRAWN BY JHNU	11/13/2020	MCHD S	NONE		HT 1 0F 1	SIZE
_			1	1			2			1		9		1		