


B

A


B

A


PANDUIT P/N	WEIGHT
P20B16M	3.8kg




REAR VIEW



TOP VIEW



FRONT VIEW




SIDE VIEW


NOTES:

1. IDENTIFICATION:  
UNIT TYPE: BASIC  
ORIENTATION: VERTICAL, HALF  
OUTLET QTY&TYPE: (20) C13  
BREAKER QTY&TYPE: (2) 20A, DOUBLE-POLE  
INPUT VOLTAGE: 200-240VAC  
INPUT CURRENT: 30A (24A DERATED)  
INPUT PHASE: SINGLE PHASE  
RATED POWER: 5.0kVA  
INPUT PLUG: NEMA L6-30P  
INPUT CORD LENGTH: 3m [10']
2. ACCESSORIES:  
POCKET GUIDE
3. RoHS COMPLIANT
4. VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
5. MAXIMUM ALLOWABLE INPUT POWER = 5.0kW
6. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES

PLUG  
30 AMP, 250V  
TWIST LOCK  
NEMA L6-30P





EIGHT (8)  
RECEPTACLES  
10 AMP, 250V  
STRAIGHT BLADE  
IEC 60320 / C13



TWELVE (12)  
RECEPTACLES  
10 AMP, 250V  
STRAIGHT BLADE  
IEC 60320 / C13

01B	08/21/2017	ZHAI	MIM	EDM	REVISED TOLERANCES	P20B16M
01A	06/28/2017	ZHAI	MIM	EDM	INITIAL RELEASE	P20B16M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY			SIGN	
			DATE	
			PRINT	
TITLE				
BASIC SERIES PDU P20B16M CUSTOMER DRAWING				
ITEM REVISION NAME				
DATASHEET FILE NAME:				
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]  Tolerance(mm) 0<50 ±0.5 50<250 ±1.0 250<500 ±1.5 500<1000 ±2.5 1000<2000 ±4.0			MATERIAL/COLOR:  N/A	
 THIRD ANGLE PROJECTION			DRAWING NUMBER: P20B16M_DC	
DRAWN BY	DATE	CHK	SCALE	
DI.ZHAI	05/24/2017	SEAN	NONE	
SHT 1 OF 1				SCALE B