


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	COLOR	MARKER SIZE	LABELS PER SHEET	SHEET PER PKG.	STANDARD PKG. QTY.
C288X040Y1J	GMYP	WHITE	2.88 [73.15] X 0.40 [10.16]	52	20	1000



NOTES:
1. MILLIMETERS ARE IN [].



.40 [10.16]
TYP. 20 PLCS.

1.37 ± .030 [34.80 ± 0.8] 2.88 [73.15] TYP. 2 PLCS. 8.50 [215.90]

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	8/17/15	RVU	SEWH	JHAC	UPDATE ON PANDUIT LOGO. CHANGE BORDER FROM B TO A. UPDATE TABLE, NOTES, ANDT TITLE. 2 PLCS. GMY8 WAS GM3SIGY2. ADD 1000. CHANGE PHONE NUMBERS.	GAECN03093
0	8/5/04	JMHO			DRAWING RELEASE.	4949

TITLE		C288X040Y1J OPTIMUM LASER/INKJET COMPONENT LABEL CONTROL DRAWING	
ITEM REVISION NAME		I00673CD/01	
DATASET FILE NAME		I00673CD_DC_C10168/01B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .12 [3.05] .xxx ± .025 [6.35] .xx ± .062 [1.57] ANGLES ±		SEE TABLE	
DRAWING NUMBER:		C10168	
DRAWN BY	DATE	CHK	SCALE
RVU	8/5/04	JHAC	1/2
SHT 1 OF 1			SIZE
SHT 1 OF 1			A