



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UICMPPT48BLY	.82 LB/EACH PC (371.1 g/EACH PC)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- PART INCLUDES:
 - 1- METAL STAMPING
 - 12- 4 POSITION FACEPLATE WITH 2 LABEL POCKETS (ASSEMBLED TO METAL STAMPING)
- B 24- CLEAR LABEL COVER
 - 1- SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - 1- SCREW KIT (INCLUDES FOUR M6 SCREWS)
- LABELS SOLD SEPARATELY.



PART NUMBER		A UICMPPT48BLY	
TITLE			
MINI-COM ULTIMATE ID 48 PORT MODULAR PATCH PANEL WITH 2 LABEL POCKETS PER FACEPLATE CUSTOMER DRAWING			
ITEM REVISION NAME		M01207AC/06	
DATASET FILE NAME		M01207AC_DC10/06C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .xxx ± .010 (.3)			
.xx ± .03 (.8)		ANGLES ±	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
		01207-10	
DRAWN BY	DATE	CHK	SCALE
JSP	7-17-02	REFR	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	8-25-14	MDJR	REFR	MMR	PREVIOUS REVISIONS OMITTED FOR CLARITY B. REMOVED COLOR LABEL COVERS FROM NOTE 4 AND CHANGED 14 TO 24 (LABEL COVERS). A. ADDED "Y" TO PART NUMBER.	01207-10

D10100DA/14