
Material	High Conductivity Seamless Copper Tube	
Plating	Electro-Tin	
Wire Size	1 AWG	38 R Ref
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	
Wire Strip Length	1-7/16 in.	
Stud Size	1/4 in.	
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.25±.0463±.0227±.02 D (2) PLS - 2.89±.06
UL Temperature Rating	90°C	
C.S.A Certified Wire Connector	Yes	
Panduit Color Code on Barrel	GREEN	→ 1.36±
Panduit Die Index No. on Barrel	P37	Wire inspection window
Alternate Industry Die Index No. () on Barrel	(11)	

LISTED

Wire Connector

CERTIFIED

.38 R Ref Color coded barrel markings 1 STR CU LCC1-14AW PANDUIT .70±.04 -+ .27±.02 DIA .25±.04 · .63±.02 (2) PLS 2.89±.06 -



								CORP. TINLEY PARK, ILLING	OIS
								LCC1-14AW-E	
01	8/12	JHNU	JHNU	REMOVED NAVY NUMBER	N10883TU-LCC1-14AW-CUST	RGB	RGB	3 Copper Lug - Two-Hole, Long Barrel with Window	~
REV	DATE	BY	снк	DESCRIPTION	ECN	-R	SUP	SCALE N/A DRAWING NO / CAD FILE LCC1-14AW-CUS	ST