

NOTES:

- 1. BRAIDED STRAP IS #4 AWG STRANDED COPPER, TIN PLATED FERRULES ARE TIN PLATED COPPER.
- 2. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
- 3. PARTS ARE UL LISTED AND CSA CERTIFIED FOR BONDING APPLICATIONS ONLY.



	BRAIDED	INSULATION	NO. OF BRAIDS IN FERRULE	DIMENSIONS - IN [mm] ± .02 [0.5]							
	STRAP SIZE			L	D	Ø	W	C	Т	H DIA	FERRULE LENGTH
BS201246EU	4 AWG	NO	1	12.00 [304.8]	10.75 [273.1]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]
BS201846EU	4 AWG	NO	1	18.00 [457.2]	16.75 [425.5]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]
BS202446EU	4 AWG	NO	1	24.00 [609.6]	22.75 [577.9]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]

