



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



VIEW ROTATED 180°

COMPLIANCE LABEL



FRONT FACEPLATE REMOVED

SPECIFICATION:

1. STANDARD:

TRANSFORMER TOPOLOGY:

KVA:

INPUT PLUG:

NOMINAL INPUT VOLTAGE:

INPUT PHASE:

OUTPUT PHASE:

NOMINAL OUTPUT VOLTAGE (GROUPS 1-4):

OUTLET TYPE AND QTY (GROUP 1-4):

NOMINAL OUTPUT VOLTAGE (GROUP 5):

OUTLET TYPE AND QTY (GROUP 5):

INPUT BREAKER TYPE:

OUTPUT BREAKER TYPE:

RING ISOLATING TRANSFORMER

5

NEMA L6-30P

208VAC

SINGLE

SINGLE

120VAC

5-20R(12)

208VAC

L6-30R(1)

25A MCB(1)

20A PUSH BUTTON(4)

2. ADDITIONAL:

NONE

3. ACCESSORY COMPONENTS:

STABILIZER BRACKET, QTY:(4)

INSTALLATION EARS, QTY:(2)

PRODUCT SAFETY WARNING SHEET, QTY:(1)

INCLUDES P/N:URMKIT2 INSTALLATION RAIL KIT, QTY:(1)

DOCUMENTATION KIT, QTY(1) - TO BE PLACED ON TOP OF ALL PACKAGING MATERIAL

REFER TO ASSOCIATED DRAWINGS FOR PHYSICAL DIMENSIONS AND SPECIFICATIONS


NOTES:

1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN INCHES


2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES

3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT.

4. ALL PURCHASED ITEMS CONFORM TO C2-0834 PANDUIT SPECIFICATION FOR CHEMICAL SUBSTANCES TO BE CONTROLLED IN PRODUCT AND PACKAGING





COMPLIANCE LABEL



DETAIL A SCALE 1:2

IDENTIFICATION:

| PART NUMBER | DESCRIPTION | SHIPPING WEIGHT (KG) |
|-------------|--|----------------------|
| UTFMRDU | TRANSFORMER DISTRIBUTION UNIT, 5kVA, 2U, 208V/120V, SINGLE PHASE | 53 |



| | | | | | | | | | | | | | |
|------------|-----|----|-----|-----|-----------------------|---------|------------|-----|----|-----|-----|-------------|-----|
| DATE | REV | BY | CHK | APR | DESCRIPTION | ECN | DATE | REV | BY | CHK | APR | DESCRIPTION | ECN |
| 05/12/2023 | | | | | RELEASE TO PRODUCTION | UTFMRDU | 01/04/2023 | | | | | | |

WE ASSURE THAT YOU OBTAIN THE BEST QUALITY AND SERVICE FROM THE CLIENT'S SUPPLIER. THIS IS OUR POLICY AND WE WILL NOT ACCEPT ANY OTHER POLICY AS IT MAY AFFECT DELIVERY.

UNLESS OTHERWISE SPECIFIED (N/A)

THIRD ANGLE PROJECTION

TRANSFORMER DISTRIBUTION UNIT
UTFMRDU
CUSTOMER DRAWING

UTFMRDU/00
UTFMRDU-DC/00A

REVISION: N/A

SECRET NUMBER: UTFMRDU-DC

SHT 1 OF 2


PANDUIT NOM

18900 PANDUIT DRIVE, 60487, USA
WWW.PANDUIT.COM

TRANSFORMER DISTRIBUTION UNIT
MODEL NUMBER: UTFMRDU
INPUT: 208 VAC | 50/60Hz | 24 A Max. | L1+L2+PE
OUTPUT:
GROUP1+GROUP2: 120 VAC | 50/60Hz | 25A Max. | L+N+PE
GROUP3+GROUP4: 120 VAC | 50/60Hz | 25A Max. | L+N+PE
GROUPS: 208 VAC | 50/60Hz | 24A Max. | L1+L2+PE
CAPACITY: 5 kVA- 5 kW

P/N: UTFMRDU
UPC# 6 113056 66123 12

PROHIBIDO SU USO EN EXTERIORES
MADE IN CHINA
HECHO CHINA



LEGEND

| SYMBOL | DESCRIPTION | SYMBOL | DESCRIPTION |
|--------|-------------------------------|--------|---------------|
| | CIRCUIT BREAKER | | SHUNT RELEASE |
| | UTILITY POWER CORD CONNECTION | | TRANSFORMER |
| | OUTPUT RECEPTACLE | | |
| | OUTPUT RECEPTACLE | | |

| | | | | | | | | | | |
|--|------------|----|-----|---------|-----------------------|---------|------|-------|------|------------------------|
| <p>WE AND YOU HEREBY AGREE THAT THE SUPPLIER SHALL BE RESPONSIBLE FOR THE QUALITY OF THE SUPPLY. THE SUPPLIER SHALL BE RESPONSIBLE FOR THE DELIVERY OF THE SUPPLY AS IT RELATES TO DELIVERY.</p> | | | | | | | | | | |
| <p>TRANSFORMER DISTRIBUTION UNIT UTFMRDU CUSTOMER DRAWING</p> | | | | | | | | | | |
| <p>REVISED DATE: UTFMRDU/00 ORDER REF: UTFMRDU-DC/00A</p> | | | | | | | | | | |
| <p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE IN (N/A)</p> | | | | | | | | | | |
| <p>SECRET NUMBER: N/A</p> | | | | | | | | | | |
| 00A | 05/12/2023 | HO | WZH | GLM/CMM | RELEASE TO PRODUCTION | UTFMRDU | | | | THIRD ANGLE PROJECTION |
| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN | DATE | SCALE | PROJ | VARIOUS |
| <p>DATE: 01/04/2023 SCALE: VARIOUS SHT 2 OF 2</p> | | | | | | | | | | |