




VIEW ROTATED 180°



DETAIL A



2D BARCODE LABEL



2X 76.3 [3.0]



SPECIFICATION:

1. STANDARD:
- | | |
|---------------------------------|----------------------------------|
| UPS TOPOLOGY: | DOUBLE CONVERSION |
| KVA: | 1 |
| BATTERY TYPE: | VALVE REGULATED LEAD ACID |
| FULL-LOAD RUN TIME (MIN): | 4.7 MINUTES |
| INPUT PLUG: | SCHUKO CEE 7/EU1-16P AND BS1363A |
| NOMINAL INPUT VOLTAGE: | 220/230/240VAC |
| INPUT PHASE: | SINGLE |
| OUTPUT PHASE: | SINGLE |
| NOMINAL OUTPUT VOLTAGE: | 220/230/240VAC |
| OUTLET TYPE AND QTY: | IEC-C13(6) SOCKET |
| DISPLAY TYPE: | 2.8 INCH, 4 BUTTON |
| PARALLEL PORT SUPPORT: | NO |
| INPUT BREAKER TYPE: | 8A PUSH BUTTON |
| OUTPUT BREAKER TYPE: | N/A |
| WEIGHT OF Pb(LEAD): | 5.1KG |
| WEIGHT OF H2SO4(SULFURIC ACID): | 1.2KG |

2. ADDITIONAL:

NONE

3. ACCESSORY COMPONENTS:

- P/N U01N12V CONTAINS AN INTELLIGENT NETWORK CARD,(INSTALLED)
- STABILIZER BRACKET,QTY:(4)
- INSTALLATION EARS,QTY:(2)
- SAFETY WARNING SHEET,QTY:(1)
- SELECTION GUIDE(POCKET GUIDE),QTY:(1)
- DB9/DB9 RS232 1.5M COMMUNICATION CABLE,QTY:(1)
- USB-A/USB-B 1.2M SERIAL COMMUNICATION CABLE,QTY:(1)
- INCLUDES P/N:UVCO36 INTERNAL BATTERY CARTRIDGE, QTY:(1),(INSTALLED)
- INCLUDES P/N:URMKIT2 INSTALLATION RAIL KIT, QTY:(1),(U01N12V ONLY)
- REFER TO ASSOCIATED DRAWINGS FOR PHYSICAL DIMENSIONS AND SPECIFICATIONS
- EPO PLUG WITH SHORTING WIRE,QTY:(1),(INSTALLED)

NOTES:

1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN INCHES
2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT
4. ALL PURCHASED ITEMS CONFORM TO C2-0834 PANDUIT SPECIFICATION FOR CHEMICAL SUBSTANCES TO BE CONTROLLED IN PRODUCT AND PACKAGING

IDENTIFICATION:

PART NUMBER	DESCRIPTION	SHIPPING WEIGHT (KG)
U01S12V	SMARTZONE IRUPS, 1kVA, 2U, 230V, SINGLE PHASE, DOUBLE-CONVERSION ON-LINE POWER PROTECTION	19.10
U01N12V	SMARTZONE IRUPS, 1kVA, 2U, 230V, SINGLE PHASE, DOUBLE-CONVERSION ON-LINE POWER PROTECTION WITH INTELLIGENT NETWORK CARD	22.30

REV	DATE	BY	CHK	DESCRIPTION	ECN	REV	DATE	BY	CHK	DESCRIPTION	ECN
01A	02/27/2021	D.L.	Z.R.Z.	A. ADDED WEIGHT OF Pb AND H2SO4 B. UPDATED DESCRIPTION C. KIT WAS URMKIT2 D. NOTCH REMOVED IN METAL	U01N12V						
00A	08/17/2021	D.L.	Z.R.Z.	RELEASE TO PRODUCTION	U01N12V						

PLEASE NOTE THAT THIS DRAWING IS ONLY THE QUALITY ASSURANCE DRAWING. THE FINAL PRODUCT SHALL BE THE PRODUCT AS SHOWN IN THE PHOTOGRAPH AND/OR THE PRODUCT AS SHOWN IN THE VIDEO.

SMARTZONE UPS
U01S12V/U01N12V
CUSTOMER DRAWING:
U01S12V/U01N12V/01
U01S12V/U01N12V-DC/01A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE IN MILLIMETERS (IN).
N/A
THIRD ANGLE PROJECTION
U01N12V-DC
SHEET 1 OF 2

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT

18300 PANDUIT DRIVE, 60487, USA
WWW.PANDUIT.COM

UNINTERRUPTIBLE POWER SYSTEMS

MODEL NUMBER: 1B1V1E

INPUT: 220/230/240 VAC | 50/60Hz | 6.0 A Max. | 1PH+N+PE

BATTERY INPUT: 36 VDC | 50 A

OUTPUT: 220/230/240 VAC | 50/60Hz | 4.6/4.4/4.2 A | 1PH+N+PE




CAPACITY: 1 kVA-1 kW
Icc: 3 kA Protective Class: I

PROHIBIDO SU USO EN EXTERIORES

MADE IN CHINA
HECHO CHINA



P/N: U01N12V



DISPLAY FIRMWARE VERSION: 3040-0243
CORE FIRMWARE VERSION: V008000000

<p>REVISIONS</p> <table border="1"> <thead> <tr> <th>REV</th> <th>DATE</th> <th>BY</th> <th>CHK</th> <th>APR</th> <th>DESCRIPTION</th> <th>ECN</th> </tr> </thead> <tbody> <tr> <td>01A</td> <td>02/17/2022</td> <td>D.L.</td> <td>ZRZ</td> <td>GLM/DJB</td> <td>"X" ADDED "WEIGHT OF THE AND H2504 B-UPDATED DESCRIPTION C-KIT WAS URMW11 DANGERS REMOVED IN METAL</td> <td>U01N12V</td> </tr> <tr> <td>00A</td> <td>08/17/2021</td> <td>D.L.</td> <td>ZRZ</td> <td>GLM/DJB</td> <td>RELEASE TO PRODUCTION</td> <td>U01N12V</td> </tr> </tbody> </table>										REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	01A	02/17/2022	D.L.	ZRZ	GLM/DJB	"X" ADDED "WEIGHT OF THE AND H2504 B-UPDATED DESCRIPTION C-KIT WAS URMW11 DANGERS REMOVED IN METAL	U01N12V	00A	08/17/2021	D.L.	ZRZ	GLM/DJB	RELEASE TO PRODUCTION	U01N12V	<p>DATE: 08/17/2021 M.D. VARIOUS</p>		<p>THIRD ANGLE PROJECTION</p>		<p>SMARTZONE UPS U01S12V/U01N12V CUSTOMER DRAWING U01S12V/U01N12V/01 U01S12V/U01N12V-DC/01A</p>		<p>SCALE: N/A</p>		<p>U01N12V-DC</p>	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN																																		
01A	02/17/2022	D.L.	ZRZ	GLM/DJB	"X" ADDED "WEIGHT OF THE AND H2504 B-UPDATED DESCRIPTION C-KIT WAS URMW11 DANGERS REMOVED IN METAL	U01N12V																																		
00A	08/17/2021	D.L.	ZRZ	GLM/DJB	RELEASE TO PRODUCTION	U01N12V																																		
<p>DATE: 08/17/2021 M.D. VARIOUS</p>										<p>U01N12V-DC</p>		<p>SHT 1 OF 2</p>																												