



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:



1. MADE FROM HIGH COPPER CONTENT ALLOY.
FURNISHED WITH FULL THREADED SILICON BRONZE BOLT,
NUTS, AND LOCKWASHERS
2. CONDUCTORS USED MUST BE OF SAME SIZE.
3. PACKAGING QTY: SEE TABLE



DB
RATED

| PART NUMBER | NOMINAL PIPE SIZE (IPS) | CONDUCTOR RANGE | WIRE DIAMETER RANGE - IN | DIMENSIONS - IN [mm] | | | | BOLT DIA | TIGHTENING TORQUE - IN-LB | PACKAGING QTY. |
|----------------|-------------------------------|--------------------|-----------------------------|----------------------|-------------|--------------|-------------|-------------|---------------------------------|-------------------|
| | | | | A | B | C | D | | | |
| GU-2-X | 1" | 4 SOL - 2/0 STR | .204 - .419 | 2.75 [70.0] | 1.13 [28.0] | 3.25 [82.0] | 1.75 [44.0] | 3/8" | 240 | 10 |
| GU-4-X | 1-1/4" | 8 SOL - 4 STR | .128 - .232 | 3.00 [76.0] | 1.13 [28.0] | 3.25 [82.0] | 2.06 [53.0] | 3/8" | 240 | 10 |
| GU-13-3 | 2" | 300 - 500 kcmil | .634 - .815 | 4.00 [102.0] | 1.50 [38.0] | 4.63 [118.0] | 2.94 [75.0] | 1/2" | 375 | 3 |

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|------|------|-----|-----|--|---------------------|
| 02 | 8/19 | JHNU | RWK | RGB | ADDED TIGHTENING TORQUE, EQUAL SIZE CONDUCTORS NOTE REVISED TITLE BLOCK | N41358BA- C41358 |

| | | | | |
|--|---------------|-----------------------|------------------------------|---|
| TITLE | | | | |
| BRONZE GROUND CLAMP CONNECTOR (GU SERIES) CUSTOMER DRAWING | | | | |
| ITEM REVISION NAME | | N41358BA/02 | |  |
| DATASET FILE NAME | | N41358BA-DC/02.SLDDRW | | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XX ±  | | | MATERIAL SEE NOTES | |
| THIRD ANGLE PROJECTION | | | DRAWING NUMBER C41358 | |
| DRAWN BY CJW | DATE 11/02 | CHK | SCALE N/A | SIZE A |
| SHEET 1 OF 1 | | | | |