

## THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	14 - 10 AWG STR, 12 - 10 AWG SOL		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length	7/16 in.		
Stud Size	1/4 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90° C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	N/A		
Panduit Die Index No. on Barrel	N/A		
Alternate Industry Die Index No. ( ) on Barrel	N/A		









						CORP. TINLEY PARK, ILLINOIS
						LCA10-14F-L
01	12/04	JHNU	JHNU	REVISED WIRE SIZE	12305	Copper Lug - One-Hole, Standard Barrel, 90° Angle Tongue
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCA10-14F-CUST