
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

	TAB SIZE	WIRE RANGE			DIMENSIONS in. [mm]			
PANDUIT PART #		ENGLISH	METRIC	HOUSING COLOR	L ± (0,8)	W ± .01 [0,3]	H± .01 [0,3]	
DNF18-188	.187 X .020 [4,8 X 0,5]	22-18	0,5-1,0	RED	.76 [19,3]	.23 [5,8]	.10 [2,5]	
DNF14-188	.187 X .020 [4,8 X 0,5]	16–14	1,5–2,5	BLUE	.76 [19,3]	.23 [5,8]	.10 [2,5]	

NOTES:

В

- 1. USED FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 194°F [90°C] MAX. OPERATING TEMPERATURE
 - C. 300 V. MAX. VOLTAGE RATING
- 2. MATERIAL:
 - A. STAMPING: .016 [0,4] THICK BRASS, TIN PLATED
 - **B. HOUSING: NYLON**
 - C. SLEEVE: TIN PLATED BRASS
- 3. INSTALLATION TOOLS:
 - A. UL LISTED AND CSA CERTIFIED:
 CT-600-A W/CT-500CH FOR DNF18
 - CT-600-A W/CT-500CH OR CT-550CH FOR DNF14
 - B. PANDUIT APPROVED:
 - CT-400, CT-460 (FOR DNF14-188 ONLY)
 - CT-1550, CT-1551, CT-2500
- 4. WIRE STRIP LENGTH: 9/32 + 1/32 [7,1 +0,8]
- 5. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- 6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT







NON-INSULATED FEMALE DISCONNECT, FUNNELED WIRE ENTRY (188 SERIES)

В

Α

CUSTOMER DRAWING

ITEM REVISION NAME

N41313BA/12

DATASET FILE NAME

N41313BA_DC_12A

						1	***************************************						
A/12	12	09.27.12	BDK	LCA	VMB	UL LISTED: REMOVED CT-500. ADDED DNF18/14 SPECIFIC NOTES PANDUIT APPROVED: REMOVED CT-100. ADDED CT-100A BROUGHT DRAWING TO CURRENT STANDARDS.	A41313	DIMEN.x ±	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 ° THIRD ANGLE		CIFIED, RE: IN [mm] .005 [.127]	SEE NOTES DRAWING NUMBER! A41313	
0001010	REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	DRAWN BY	DATE -	CHK -	SCALE N.T.S.	SHEET 1 OF 1	SIZE A

2