THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART #	WIRE RANGE AWG [mm <sup>2</sup> ]	DIMENSIONS in. [mm]		
		L ± [0,51]	B DIA.± .01 [0,25]	C ± .01 [0,25]
BS18	#22-18 [0,5-1,0]	.62 [15,7]	.14 [3,6]	.032 [0,81]
BS14	#16-14 [1,5-2,5]	.62 [15,7]	.16 [4,1]	.032 [0,81]
BS10	#12-10 [4,0-6,0]	.63 [16,0]	.22 [5,6]	.040 [1,02]

## NOTES:

В

- 1. USED FOR:
  - A. SOLID OR STRANDED COPPER WIRE
  - B. 302°F [150°C] MAX. TEMPERATURE RATING
- 2. INSTALLATION TOOLS:
  - A. UL LISTED AND CSA CERTIFIED: CT-100A, CT-200, CT-600A (CT-570CH), CT-1570, CT-2500(CT-2570CH)
  - B. PANDUIT APPROVED: CT-160, CT-260
- 3. WIRE STRIP LENGTH: 9/32 17,1 10,8]
- 4. MATERIAL:
  - A. STAMPING: COPPER, TIN PLATED
- 5. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- 6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT

2



В

