

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
HC2**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	0.79 LB (358g)	0.12 LB/FT (1.8g/cm)
HC2**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	0.72 LB (327g)	0.12 LB/FT (1.8g/cm)
HC2**3 (SEE NOTE 1)	118.11 IN ±.18 IN (3000mm ±4.6mm)	1.18 LB (536g)	0.12 LB/FT (1.8g/cm)
HC2**10 (SEE NOTE 1)	120.00 IN ±.18 IN (3048mm ±4.6mm)	1.20 LB (545g)	0.12 LB/FT (1.8g/cm)

**NOTES:**

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	5/11/2021	MES	PATR	PATR	ADDED PART NUMBERS HC2**3, HC2**10	V09002MM/00
1	03-05-13	JBN	RTFI	RN	A. UPDATED DRAWING BORDER & TITLE BLOCK	38258-23
R	01-08-07	MSO	RN	RN	RELEASED TO PRODUCTION	38258-23

TITLE		<b>FIBERRUNNER 2X2 HINGED COVER</b> (HC2**2, HC2**6, HC2**3, HC2**10) CUSTOMER DRAWING	
ITEM REVISION NAME			
D38258CH/00			
DATASET FILE NAME			
D38258CH_DC/00C		MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		PVC	
.X ± .XX ± .03 [ .8 ]		DRAWING NUMBER:	
.XXX ± ANGLES ±		38258-23	
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
MSO	01-08-07	RN	NONE
SHT 1 OF 1		SIZE	
		A	

2

1

D10100DA/15