




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DETAIL VIEW OF LABEL AREA



THIS PATCH PANEL WILL ONLY ACCEPT RJ45 COPPER CONNECTORS. FIBER AND AV MODULES WILL NOT FIT CORRECTLY TO ACCEPT THEIR MATING PLUG.

PANDUIT P/N	WEIGHT
CPPA48HDEWBL	6.88 LB/10 PCS (3215.2.0 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:
 - (1) -48 PORT ANGLED STAMPING
 - (6) -8 POSITION FACEPLATE (ASSEMBLED TO PANEL)
 - (1) -SCREW KIT (INCLUDES FOUR #12-24 SCREWS AND FOUR LOCK WASHERS)
 - (1) -SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN [] ARE IN METRIC.

PART NUMBER		CPPA48HDEWBL	
TITLE			
MINI-COM 48 PORT ANGLED HIGH DENSITY MODULAR PATCH PANEL WITH ENHANCED LABELING AREA			
CUSTOMER DRAWING			
ITEM REVISION NAME		M00741FV/00	
DATASET FILE NAME		M00741FV_DC/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xx ± .03 [.8]		PANEL: 20 GAGE C.R.S. FACEPLATE: ABS	
.xxx ± .010 [.3]		DRAWING NUMBER:	
ANGLES ±		00741-116	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
JSP	8-31-06	MJD	NONE
REV	DATE	BY	APR
1	5/7/14	JSP	REFR
R	8-31-06	JSP	MJD
DESCRIPTION		ECN	
A. REVISED DRAWING TITLE BLOCK.		00741-116	
RELEASED TO PRODUCTION		00741-116	



D10100DA/14