




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS: SEE SHEET 2
4. MATERIALS:
 - A. BOX AND LID: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
5. CASSETTE WEIGHT: 3.53oz [100g]
6. DIMENSIONS IN BRACKETS ARE METRIC.

**FRONT VIEW**

TITLE					HD FLEX 8 FIBER LC CONVERSION CASSETTE				
					CUSTOMER DRAWING				
ITEM REVISION NAME					12F187HS/00				
DATASET FILE NAME					12F187HS_DC/00B				
ALL DIMENSIONS ARE FOR REFERENCE					MATERIAL:				
					SEE NOTES				
					THIRD ANGLE PROJECTION				
					DRAWING NUMBER:				
					12F187HS-DC				
DRAWN BY		DATE		CHK		SCALE		SIZE	
SAT		01-09-15		PIP		NONE		SHT 1 OF 2	
								A	

00	01-09-15	SAT	PIP	RAR	RELEASED TO PRODUCTION	12F187HS-DC			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN			

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

HD FLEX 8 FIBER LC CONVERSION CASSETTE - METHOD B	
FHC3X0-08-10BN	8 FIBER / OM3 OPTIMIZED LOSS
FHC3Z0-08-10BN	8 FIBER / OM4 OPTIMIZED LOSS
FHC3ZA-08-10BN	8 FIBER / OM4 ULTRA LOW LOSS

HD FLEX 8 FIBER LC CONVERSION CASSETTE - METHOD A	
FHC39N-08-10AN	8 FIBER / OS2 STANDARD LOSS



FIBER WIRING

							TITLE		HD FLEX 8 FIBER LC CONVERSION CASSETTE	
							CUSTOMER DRAWING			
							ITEM REVISION NAME		12F187HS/00	
							DATASET FILE NAME		12F187HS_DC/00B	
							ALL DIMENSIONS ARE FOR REFERENCE		MATERIAL :	
									SEE NOTES SHEET 1	
									DRAWING NUMBER:	
									12F187HS-DC	
00	01-09-15	SAT	PIP	RAR	RELEASED TO PRODUCTION		12F187HS-DC			
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	DRAWN BY	DATE	CHK
								SAT	01-09-15	PIP
								SCALE	NONE	
								SHT 2 OF 2		SIZE
										A