Γ						2		1
		THIS COPY	Y IS	PROVI	DED C	N A RESTRICTED BASIS AND IS NOT TO BE US	ED IN ANY W	WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.
								PANDUIT WEIGHT
в				[13	3 DI 3.5] mm 1.1 [29.		E CURREN D INDICATE E FIBERRU S USED TO BLE ROUT E I/2" (M 13" (330) E FIBERRU ICLUDES: NE (1) BR/ DUR (4) 1/ DUR (4) M	FR6TB12 FR6TB12M1.23 LB/EACH (559g/EACH)IT CATALOG FOR ADDITIONAL PART SUFFIXES E PACKAGE QUANTITY. UNNER 4×4 AND 6×4 QUIKLOCK TRAPEZE BRACKET SUPPORT THE FIBERRUNNER 4×4 AND/OR 6×4 ING SYSTEMS BETWEEN TWO (2) SECTIONS OF M12) THREADED ROD THAT ARE 10" (254) 0.2) APART. UNNER 4×4 AND 6×4 QUIKLOCK TRAPEZE BRACKETCACKET ASSEMBLY, /2 HELICAL SPRING LOCKWASHERS, /2-13 HEAVY HEX NUTS (FR6TB12 ONLY), M12×1.75 HEX NUTS (FR6TB12M ONLY). OR: BLACK (EXCEPT FOR HARDWARE).
<u> </u>			≞ ~		[249 - 13. [350	78	MENS I ONS	STAMPING OPTIONAL
A								TITLE FIBERRUNNER 4x4 AND 6x4 QUIKLOCK TRAPEZE BRACKET 1/2" (M12) THREADED ROD CUSTOMER DRAWING ITEM REVISION NAME D38022CN/04 DATASET FILE NAME D38022CN_DC/04B
02/70	04B	9/12/19	MEX- JAGC	FWI	FWI	P. "STAMPING OPTIONAL" LABEL ADDED SEE PREVIOUS REVISION FOR HISTORY	V09002CN/07	-1 \square \square PROJECTION $ $ $38022-48$ $ $
D10100DA/20	REV	DATE	BY	снк	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE SIZE JHNU 10-02-01 RPA NONE SHT 1 OF 1 A
					I	2		1