Mini-Com[®] Classic Series Faceplates



specifications

Classic series faceplates shall be available in 1, 2, 3, 4, and 6-port single gang for vertical applications and 2-port single gang for horizontal applications. Classic series faceplates shall accept all Mini-Com[®] Modules for UTP, STP, fiber-optic, and audio/video applications. Faceplates shall be available in a flush or sloped design, and available with or without labels. Sloped design shall increase wall depth to improve the bend radius control.



technical information

Mounting options:	Screw holes with retention tabs, spaced for single gang openings; compatible with Panduit wall board adapter		
Packaging:	Supplied with two 1" long, #6 – 32 slotted head screws; select styles include labels and label covers; faceplates without labels include matching mounting screws to match the faceplate; faceplates packaged one per bag, ten per box.		
	Eco packaging supplied with 10 faceplates, 20 mounting screws in a paper envelope, 20 labels and 20 label covers in paper envelope.		

key features and benefits

Modular	Accepts all Mini-Com [®] Modules which snap in and out for easy moves, adds, and changes		
Identification	Choice of adhesive labeling or dedicated label pocket for easy identification		
Various port densities	Provides design flexibility		
Sloped design	Allows proper bend radius control		
Icon slots	Provide data and voice identification on select faceplates		
Eco packaging	Select product with plastic packaging removed, easy access to all components while reducing waste		

applications

Mini-Com[®] Classic Series Faceplates mount to any standard size single gang junction box and can also mount to a wallboard adapter or raceway mounting brackets. When using classic series faceplates with Panduit surface raceway, color matching is guaranteed. Classic series faceplates with label and label cover offer a quick and easy way to identify the ports. Mounting screw colors match the faceplate for a clean, consistent look.


Dedicated sloped faceplates provide additional room for bend radius control to help comply with standards. Select sloped faceplates include icon slots to help identify the connection.

Eco packaging available for select product, provides easy access to the product and components while reducing waste.


Vertical Sloped Facep Labels and Icon Slots	lates with
2-port:	CFPSL2IWY
4-port:	CFPSL4IWY
Vertical Faceplates wi	th Labels
1-port:	CFPL1IWY
2-port:	CFPL2IWY
3-port:	CFPL3IWY
4-port:	CFPL4IWY
6-port:	CFPL6IWY
Eco Packaging	
2-port:	CFPL2IW-X
2-port:	CFPL2WH-X
4-port:	CFPL4IW-X
4-port:	CFPL4WH-X
Vertical Faceplates wi	thout Labels
1-port:	CFP1IW
2-port:	CFP2IW
4-port:	CFP4IW
Horizontal Faceplates	
2-port:	CFPH2IW
4-port (sloped with labels):	CFPHSL4IW
Wall Board Adapters	
Single gang:	MWBA1

See table for color and labeling options.


vertical faceplates




horizontal faceplates



vertical sloped faceplates





Dimensions are in inches. [Dimensions in brackets are metric].

color and labeling options

Part Number	IW	WH	EI	Opening	Replacement Label	Laser/Ink jet	Panther LS8E
CFP1**					-	C061X030FJJ	C061X030FJC
CFP2**						C125X030FJJ	C125X030FJC
CFP4**							
CFPH2**							
CFPH4**						C252X030FJJ	C252X030FJC
CFPHSL4**					C4PPLK	C261X035Y1J	C261X035Y1C
CFPL1**Y					Single Gang EFPK-XY (Includes Screws)		
CFPL2**Y							
CFPL3**Y				Single Gang			
CFPL4**Y							
CFPL6**Y							
CFPSL2**Y						C195X040Y1J	C195X040Y1C
CFPSL4**Y					(
CFPL2IW-X							
CFPL2WH-X							
CFPL4IW-X							
CFPL4WH-X							

Gray shaded area depicts colors are not available.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2022 Panduit Corp. ALL RIGHTS RESERVED. OTSP20--WW-ENG 1/2022