
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DANIDUIT.	WIRE RANGE AWG [mm ²]	DIMENSIONS in. [mm]				
PANDUIT PART #		L ± [0,76]	B DIA. ± [0,25]	C ± .03 [0,76]	D DIA. ± .01 [0,25]	
BS22	#26-22 [0.25-0.5]	47 [11.9]	08 [2.0]	.02 [0.5]	04 [1.0]	





 B

1. USED FOR:


A. #26-22 [0,25-0,5mm²] SOLID OR STRANDED COPPER WIRE B. 302°F [150°C] MAX. TEMPERATURE RATING

2. INSTALLATION TOOLS: A. PANDUIT APPROVED: CT-100A, CT-200, CT-160, CT-260

- 3. WIRE STRIP LENGTH: 9/32 +1/32 [7,1 +0,8]
- 4. MATERIAL:

A. STAMPING: .02 [0,5] COPPER, TIN PLATED

- 5. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- 6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



								_		
A								BUTT SPLICE, NON- INSULATED #26-22		
								CUSTOMER DRAWING		
								ITEM REVISION NAME N41336BA/08 DATASET FILE NAME		
								N41336BA_DC/08A		
	08	10.08.19	JHNU	RGB	RGB	REVISED DIMENSION NAME IN TABLE: D DIA WAS B DIA	N41336BA-A41336			
	07	10.20.14	JHNU	JHNU	RGB	REMOVED UL & CSA FROM NOTE 2	N41336BA-A41336	1	SEE NOTES	
DA/15	06	09.06.12	JBN	LCA	VMB	REVISED NOTES. ADDED METRIC EQUIVALENTS. UPDATED DRAWING TO CURRENT STANDARD.	A41336	THIRD ANGLE PROJECTION A41336		
_ D10100	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE DAW - N.T.S SHT 1 0F 1		