


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



WEIGHT OF 2.5km REEL/BOX	
OFNP	OFNR
55.5 kg (122.3 lbs)	51.9 kg (114.4 lbs)


TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
MULTIMODE 62.5/125um DUPLEX ZIPCORD INTERCONNECT CABLE W/900um TIGHT BUFFER	ORANGE	3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm

PLENUM - FSIP602Y			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
220 N (50 lbf)	55 N (12.5 lbf)	58 mm (2.3 in)	29 mm (1.1 in)
CABLE DIMENSIONS		TEMPERATURE	
"A" = 2.9mm [ .11" ] "B" = 5.9mm [ .23" ]		INSTALLATION/OPERATION	STORAGE
		0°C TO +50°C 32°F TO +122°F	-40°C TO +65°C -40°F TO +149°F

RISER RATED - FSIR602Y			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
220 N (50 lbf)	55 N (12.5 lbf)	58 mm (2.3 in)	29 mm (1.1 in)
CABLE DIMENSIONS		TEMPERATURE	
"A" = 2.9mm [ .11" ] "B" = 5.9mm [ .23" ]		INSTALLATION/OPERATION	STORAGE
		-20°C TO +50°C -4°F TO +122°F	-40°C TO +65°C -40°F TO +149°F

NOTES:

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. CABLE SUPPLIED IN 2500 METER (8202 FT) LENGTHS.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

PART NUMBER		FSIP602Y , FSIR602Y			
TITLE					
MULTIMODE 62.5/125um OPTI-CORE DUPLEX ZIPCORD INTERCONNECT CABLE W/900um TIGHT BUFFER  CUSTOMER DRAWING					
ITEM REVISION NAME		M02055BC/01		<b>PANDUIT</b>	
DATASET FILE NAME		M02055BC_DC_2Z-625/01A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]  .X ±                      .XXX ± .XX ±                     ANGLES ±  				MATERIAL :	
				DRAWING NUMBER:  02055 - 18	
DRAWN BY	DATE	CHK	SCALE	SIZE	
MC	08-26-04	WMA	NONE	SHT 1 OF 1	
				A	