						2		1	
		THIS CO	PY IS	5 PRO'	VIDED	ON A RESTRICTED BASIS AND IS NOT TO BE US	ED IN ANY W	AY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.	
в						YEL	PRINT .low	NOTE: 1. MILLIMETERS ARE IN [ ].	B
<		2				4.5► [114.3]			
		PART NUMBER WL33Y			ERIA	4.5 [114.3] BLACK LINES	R 8 PER 50/	CKAGE NTITY /ROLL	
				/ I IN Y L	_ GM	VI PER SIDE BLACK LINES	CH		
A								TITLE WL33Y WARNING LABEL   IS03864 CAUTION RISK OF ELECTRICAL SHOCK   CONTROL DRAWING   ITEM REVISION NAME   100318KC/01   DATASET FILE NAME   100318KC-DC-C10144/01C	A
	2	5/28/13	RVU	MJPF		REPLACE WL33 WITH WL33Y.	GAECN00882	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .1 [2.54] .xxx ± .005 [.127] SEE TABLE.	
	1 R	10/2/03 7/17/92	RVU JM		DWY DWY	CHANGED DWG. NO. TO C10144. DRAWING RELEASE.	3429 0000	.XX ± .01 [.25] ANGLES ± 5 °	
								DRAWN BY   DATE   CHK   SCALE   SIZE	
	REV	DATE	BY	СНК	APR		ECN	JM   7/15/92   DWY   NTS   SHT 1 0F 1   A	
						2		1	