



PANDUIT P/N	WEIGHT
CWMPV3418	2.45 LB/EACH PC (1111.3 g/EACH PC)

- NOTES:
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
 - PART INCLUDES:
2- COVER
1- CABLE MANAGER
1- SCREW KIT

MAX STORAGE TEMPERATURE 65°C (149°F)
MAX OPERATING TEMPERATURE 60°C (140°F)



TITLE				18 R.U. IN-CABINET VERTICAL MANAGER (FRONT ONLY) (CWMPV3418)		CUSTOMER DRAWING	
ITEM REVISION NAME				M00720AL/00			
DATASET FILE NAME				M00720AL_DC/00B			
MATERIAL				DUCT : PVC			
DRAWING NUMBER				00720-43			
DRAWN BY				DATE		SCALE	
JSP				3-22-00		NONE	
SHEET 1 OF 1				SIZE		A	

A-SIZE CUSTOMER

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00B	5-14-20	JBO	JCO	JEKF	ADDED TEMPERATURE NOTE	M09000LT