

THIS COPY IS PROVIDED ON A	A RESTRICTED BASIS AND IS NOT TO BE U	ISED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.
Material	High Conductivity Seamless Copper Tube	
Plating	Electro-Tin	
Wire Size	400 kcmil	63 R
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	
Wire Strip Length	2-3/8 in.	PANDUIT  (S) 400 kcmi Sir Cu (CC400-12w Cu (
Stud Size	1/2 in.	
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.63±.04 .53±.02 .53±.0 (2) PL
UL Temperature Rating	90° C	5.84±.06
C.S.A Certified Wire Connector	Yes	
Panduit Color Code on Barrel	BLUE	-
Panduit Die Index No. on Barrel	P76	Wire inspection window—
Alternate Industry Die Index No. ( ) on Barrel	(19)	









						CORP. TINLEY PARK, ILLINOIS
						LCC400-12W-6
01	12/05	JHNU	ЛНИП	REVISED TONGUE WIDTH: 1.39 WAS 1.28 REVISED TONGUE THICKNESS: .18 WAS .17	PC00222	Copper Lug - Two-Hole, Long Barrel with Window
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCC400-12W-CUST