

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	500 kcmil
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	2-9/16 in.
Stud Size	1/2 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P87
Alternate Industry Die Index No. () on Barrel	(20)









LISTED Wire Connector

REV	DATE	BY	СНК	DESCRIPTION	ECN	S
00	5/16	JHNU	JHNU	DRAWING RELEASED		
01	11/16	JHNU	JHNU	REVISED HOLE OFFSET & BARREL LENGTH TOLERANCE: ±.07 WAS ±.04 REVISED OVERALL LENGTH TOLERANCE: ±.09 WAS ±.06 REVISED WIRE STRIP LENGTH: 2-5/8 WAS 2-9/16	00127LBS- LCB500-12W-CUST	
02	, .,				LCB300-12W-C031	
02	12/17	JHNU	JHNU	REVISED WIRE STRIP LENGTH: 2-9/16 WAS 2-5/8	00127LBS- LCB500-12W-CUST	



$oxedsymbol{oxed}$ CORP. TINLEY PARK, ILLINOIS

LCB500-12W-6 Copper Lug - One-Hole, Long Barrel with Window

SCALE DRAWING NO / CAD FILE

LCB500-12W-6