					2		1	
	THIS (OPY IS	5 PRO	VIDED	ON A RESTRICTED BASIS AND IS NOT TO	BE USED IN ANY	WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.	
B	6.			— 2			PANDUIT P/NWEIGHTCFPGAS6S**.84 LB/10 PCS(383.7 g/10 PCS)NOTES:1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.2. SEE CATALOG FOR COMPLETE LIST OF	B
4					B. REVISED AND REDRAWN, PREVIOUS REVISIONS		CUSTOMER DRAWING CUSTOMER DRAWING ITEM REVISION NAME M01012AA/05 DATASET FILE NAME M01012AA_DC/05B UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03[.8] ANGLES ±	А
*1/V0001010 RE			REFR	MMR	HAVE BEEN OMMITTED.	01012-05	DRAWN BY DATE CHK SCALE SIZE	
	IV DATE	BY	СНК	APR		ECN	JSP 10-2-01 MJD NONE SHT 1 0F 1 A	
					2		1	