

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT	COPPER CONDUCTOR RANGE	DIMENSIONS - IN [mm] ±.1 [2.5]			BOLT
PART NUMBER		L	W	Н	DIA
GBC2250-12-X	2/0 STR - 250 kcmil	2.04 [52]	1.25 [32]	2.27 [58]	1/2"
GBC4300-12-X	4 STR - 300 kcmil	2.16 [55]	1.38 [35]	2.82 [72]	1/2"
GBC3500-12-X	300 kcmil - 500 kcmil	2.69 [68]	1.64 [42]	2.82 [72]	1/2"



NOTES:

- 1. MATERIAL:
 - -BODY HIGH COPPER CONTENT ALLOY -HARDWARE SILICON BRONZE
- 2. PARTS ARE CULUS LISTED TO UL467/CSA22.22 No. 41 AS GROUNDING AND BONDING EQUIPMENT.
- 3. CONNECTORS ACCOMODATE TWO EQUAL DIAMETER CONDUCTORS IN THE RANGE SPECIFIED.
- 4. ACCOMODATES BAR THICKNESS OF 0.250 [6.35] MAX.
- 5. RATED FOR DIRECT BURIAL
- 6. SEE PACKAGING LABEL FOR TIGHTENING TORQUE SPECIFICATIONS.
- 7. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
- 8. PKG. QTY. = 10



							GROUND BAR CLAMP CUSTOMER DRAWING	
							ITEM REVISION NAME 13J051AL/03	
						l I	DATASET FILE NAME 13J051AL-DC/03.SLDDRW	
03	7/18	JHNU	BKR	RGB	ADDED GBC4300-12-X, GBC3500-12-X	038340	UNLESS OTHERWISE SPECIFIED, MATERIAL	
02	1/16	JHNU	BKR	RGB	ADDED PACKAGING QTY. TO PART NUMBER	13J051AL-DC	DIMENSIONAL TOLERANCES ARE: IN [mm]	
01	1/16	JHNU	BKR	RGB	REVISED NOTE 2: REMOVED 13	13J051AL-DC	.XX ± .XXX ± SEE NOTES .XXX ± ANGLES ±	
00	10/15	JHNU	BKR	RGB	DRAWING RELEASED	13J051AL-DC	THIRD ANGLE PROJECTION DRAWING NUMBER 13J051AL-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	JHNU 4/15 BKR N/A SHEET 1 OF 1 SIZE	