



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART



CUTOUT

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [] ARE METRIC.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
4. MATERIAL:
 FRAME - POLYPROPYLENE (PP)
 BLOCK - TPE
5. PROTECTION CLASS WHEN USED WITH CEG GROMMETS:
 NEMA 1,12,4x*
 IP 65
6. TEMPERATURE RANGE: -22 - 212 °F
7. FLAMMABILITY: V0
8. RoHS COMPLIANT
9. COMPLIANCE cURus
10. UV RESISTANT
11. WEIGHT: SEE TABLE

*Indoor Use



PART NUMBER	A	B	INSTALLATION HEIGHT in. (mm)	NUMBER OF OPENINGS			D	c	d	e	PART WEIGHT lbs. (g)	PKG QTY
	in. (mm)	in. (mm)		SMALL	MEDIUM	LARGE	in. (mm)	in. (mm)	in. (mm)	in. (mm)		
CEST2-R504	2.44 (62)	2.44 (62)	0.71 (18)	4	-	-	1.99 (50.5)	0.91 (23)	0.91 (23)	0.22 (5.6)	0.137 (62)	1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	9/13/2022	SERH	MDS	JADE	INITIAL RELEASE	124032/00

PART NUMBER		SEE TABLE	
TITLE		CEST2-R Control Drawing	
		CUSTOMER DRAWING	
ITEM REVISION NAME		00872EBD/00	
DATASET FILE NAME		00872EBD_DC/00A	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE NOTE 4	
DRAWING NUMBER		00872EBD-DC	
DRAWN BY	DATE	CHK	SCALE
SERH	9/13/2022	MDS	1:1
SHEET 1 OF 1			SIZE B

B

B

A

A

B-SIZE CUSTOMER