

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DUST CAPS NOT SHOWN FOR CLARITY

2



DESCRIPTION

NOTES:

PART NUMBER

ITEM REVISION NAME

DATASET FILE NAME

•X ±

.XX ±

DRAWN BY DATE

MC

ECN

M01945AW/02

M01945AW_DC/02A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]

.XXX ±

THIRD ANGLE

PROJECTION

NONE

SCALE.

1

ANGLES ±

TMSE


CHK

08-02-06

- 1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- 3. MATERIALS:
 - A. PLATE: C.R.S. POWDER COATED.
 - B. ADAPTER: COMPOSITE WITH METAL CLIP.
 C. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITTEE.

В

- 4. ADAPTERS ARE SUPPLIED WITH TWO DUST PLUGS.
- 5. DIMENSIONS IN [] ARE METRIC.
- 6. WHITE MARK ON MPO ADAPTER CORRELATES TO FIRST FIBER ON INSTALLED MPO/MTP CONNECTOR.



FAPHO612BLMPO, FAPHO612CGMPO

6 POSITION, 72 FIBER HORIZONTAL MPO FIBER ADAPTER PANEL

MATERIAL:

DRAWING NUMBER:

01945-64

SHT 1 0F 1

SIZE

CUSTOMER DRAWING

DATE

ΒY

CHK

0100DA/14

Α

B

APR