	2							1						
	THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE US							D IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.						
										PA	NDU I T	P/N	WEIGHT	
				I							CFPL2	2SY	1.0 LB/10 PCS (458.1g/10 PCS)	
B			4.5]					.33 3.4]	2. 9 3. 1 4. 1	SEE CURF PART NUN COLOR AN SEE CAT PARTS AF PART. DIMENSIO PART INO 1 - FACEF	MBER S ND OR ALOG F PPLIC DNS II CLUDES PLATE 2 X 1 -	SUFFIXES PACKAGE FOR COMF ABLE FOF N [] ARE S: MOUNT	FOR ADDITIONAL 5 TO INDICATE QUANTITY. PLETE LIST OF R USE WITH THIS E IN METRIC. ING SCREWS	B
v14	2	4/14/14	JSP	REFR	MMR	REVISED AND REDRAWN; ALL OTHER DRAWING REVISI HAVE BEEN OMITTED.	.76 [19.2] ■		DATASET FIL UN DIMENS	I-COM 2 FA(0N NAME M024 M02479FI	POSITI CEPLA CL 79FI/00 LDC141/00 VISE SPE RANCES A .XXX ± ANGLES ± TH1	C C C C C C C C C C C C C C	ILESS STEEL VERTICA LABEL/COVER RAWING PRODUCT	T
D10100DA/14	REV				ECN	DRAWN BY D		СНК	SCALE	SHT 1 0F 1	SIZE A			
D10	· _ ¥	DATE				2			125	3–14–06	MJD	NONE 1	5HI 1 UF 1	A
												<u></u>		