
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	4/0 AWG		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length	1-5/8 in.		
Stud Size	3/8 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90° C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	PURPLE		
Panduit Die Index No. on Barrel	P54		
Alternate Industry Die Index No. () on Barrel	(15)		






LISTED Wire Connector







$\overline{}$					-			-
REV	DATE	BY	СНК	DESCRIPTION	ECN	-R	SUP	S
00	4/17	JHNU	JHNU	DRAWING RELEASED	021775	RGB	RGB	

CORP. TINLEY PARK, ILLINOIS

LCB4/0-38WH-X Copper Lug - One-Hole, Long Barrel with Window, 45° Angle Tongue

SCALE N/A DRAWING NO / CAD FILE

LCB4/0-38WH-CUST